

1U Server Rack Shelf - Universal Rack Mount Cantilever Shelf for 19" Network Equipment Rack & Cabinet - Durable Design - Weight Capacity 55lb/25kg - 12" Deep Tray

Product ID: SHELF-1U-12-FIXED-S



The SHELF-1U-12-FIXED-S lets you add a 1U 12 inches (30.5 cm) deep shelf to any EIA-310 compliant 19-inch rack or cabinet.

Quality construction

The fixed-rack shelf can hold up to 55 lbs (25 kg) of equipment and is constructed using 2.0 mm SPCC commercial-grade cold-rolled steel for long-term durability and sturdiness. Accommodate your accessories or non-mountable devices for ease of access or connectivity to your equipment.

Two installation options

You can install the 1U rack shelf using one of two different orientations for mounting. The standard, with the lip facing downwards or inversed with the lip facing upwards that prevents your equipment from sliding off.

Hardware included

Conveniently includes M6 square cage nuts and M6 screws to setup your equipment in no time.

The SHELF-1U-12-FIXED-S is backed by a StarTech.com lifetime warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

Features

- **UNIVERSAL 19" FIT:** This 1U server rack mount shelf is designed to fit EIA-310 compliant 19in server racks and can accommodate an internal depth of 12in (30.5cm) for your data, IT, networking, or other equipment from brands like APC, Dell, Lenovo and HPE
- **DURABLE DESIGN:** Constructed with 2.0 mm thick SPCC commercial cold-rolled steel, the sturdy front mounted cabinet shelf ensures durability and supports a total weight of 55 lbs (25 kg) making it the perfect rack shelf for any environment
- **STRUCTURAL INTEGRITY:** Constructed with downward facing front and rear lips that uses up minimal height space preserving vertical shelf space for your equipment; Downward lips will not interfere when placing or taking equipment on or off the shelf
- **EASY ACCESS:** The shelf can be used for modems, routers, Wi-Fi access points, and other IT/network/telco equipment that can't be mounted on a rack or to store and access frequently used tools and supplies
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, This 1U universal server rack is backed for life, including free lifetime 24/5 multi-lingual technical assistance

Hardware

Warranty	Lifetime
U Height	1U
Cable Management	No

Performance

Weight Capacity (Stationary)	55.1 lb [25 kg]
------------------------------	-----------------

Physical Characteristics

Product Length	12.0 in [30.5 cm]
Product Width	19.0 in [48.3 cm]
Product Height	1.7 in [4.3 cm]
Weight of Product	5.5 lb [2.5 kg]

Packaging Information

Package Quantity	1
Package Length	21.7 in [55.0 cm]
Package Width	14.6 in [37.0 cm]

Package Height	4.7 in [12.0 cm]
Shipping (Package) Weight	7.1 lb [3.2 kg]

What's in the Box

Included in Package	1 - Shelf
	4 - M6 Square Cage Nuts
	4 - M6 Cage Screws
	4 - Plastic Washers
	1 - Quick-Start Guide

****Product appearance and specifications are subject to change without notice.***