

1U Sliding Server Rack Mount Keyboard Shelf Tray, 55lbs (25Kg), 22in (55cm) Deep Steel Pull Out Drawer for 19" AV, Network Equipment Rack

Product ID: SLIDESHELF



The Black SLIDESHELF 22in Deep Sliding Server Rack Cabinet Shelf lets you add a 2-in-1 slide-shelf / keyboard tray that helps you keep costs down and productivity up.

As your server cabinet needs change, the SLIDESHELF changes to suit by allowing you to use it as a sturdy sliding shelf, or a 1U pull out drawer with a weight capacity of 55 pounds. Simply flip the installed drawer over and it becomes a shelf to hold monitors, laptops and other diagnostic equipment. An easy-to-hide handle pulls out to help you get a grip on the situation and hides away quickly.

The rack shelf includes all of the tools needed for installation, and is compatible with standard 19in racks and cabinets with a 22in depth, including the StarTech.com 7236CABINET, RK2236BKF, RK4236BK, and RK4236BKNS DuraRak cabinets.

Certifications, Reports and Compatibility



Applications

- For use with all 19" wide Server Racks and Cabinets
- Supply additional sliding storage space for mission critical hardware

Features

- **UNIVERSAL 19" FIT:** Add a sliding shelf to any 19in server rack or cabinet for easy peripheral and equipment access; This pull out tray can function as a sliding shelf, or a 1U drawer when inverted
- **HEAVY-DUTY & DURABLE DESIGN:** Constructed with solid steel, the sturdy IT-grade pull out keyboard tray ensures long term durability and supports a total weight load of 55lb (25kg)
- **COMPACT DESIGN:** The 1U server rack shelf features a compact form factor, making it ideal non-rackmount equipment, tools and peripherals in your home, studio or office space
- **VERSATILE FUNCTIONALITY:** This 22in (55cm) deep slide out tray can switch from a sliding shelf to a sliding drawer; It's ideal for adding additional sliding storage space for your IT or AV accessories
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this sliding server rack shelf is backed for life, including free lifetime 24/5 multi-lingual technical assistance

Hardware

Warranty	Lifetime
Frame Type	Steel
U Height	1U
Cable Management	No

Performance

Weight Capacity (Stationary)	55.1 lb [25 kg]
------------------------------	-----------------

Physical Characteristics

Color	Black
Material	Steel
Product Length	21.7 in [55.1 cm]
Product Width	19.0 in [48.3 cm]
Product Height	1.7 in [4.4 cm]
Weight of Product	12.6 lb [5.7 kg]
Maximum Mounting Depth	32.2 in [81.8 cm]
Minimum Mounting Depth	21.7 in [55.2 cm]

Packaging Information

Package Quantity	1
Package Length	24.2 in [61.5 cm]
Package Width	19.1 in [48.4 cm]
Package Height	3.3 in [8.3 cm]
Shipping (Package) Weight	14.4 lb [6.5 kg]

What's in the Box

Included in Package	1 - 1U Sliding Shelf
	2 - Front and Rear Mounts
	2 - Rails
	1 - Pack of hardware including screws, nuts, and bolts
	8 - M5 Screws w/ washer
	8 - M5 Cage Nuts

Warranty Information

Warranty	Lifetime
----------	----------

****Product appearance and specifications are subject to change without notice.***