

USB 3.0 to Slimline SATA ODD Enclosure

Product ID: SLSODDU33B



This durable optical drive enclosure helps make your laptop, Ultrabook or tablet even more powerful by adding an external USB 3.0 Optical Disk Drive (ODD). Simply slide your slimline SATA Blu-ray, CD or DVD-ROM drive into this compact portable enclosure to add optical reading and writing support to your computer.

With USB 3.0 as the output interface, the drive enclosure supports up to 5Gbps transfer rate. Now you can access videos and other large files quickly to save valuable time while you're on the go.

With a durable, solid-aluminum housing, this top-quality external enclosure gives you the compact portability you need when you're on the move or in the field. Plus, the enclosure is USB-powered, so you won't have to carry a power adapter with you everywhere you go.

The optical drive enclosure is OS independent, so you can rest assured it's compatible with any operating system including Mac, Windows, Linux and Android.

It's also backward compatible with USB 2.0 and 1.1, so you'll be able to connect your optical drive to older computers.

The SLSODDU33B drive enclosure is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Add a Blu-ray or DVD-ROM drive to your Ultrabook or laptop through USB 3.0
- Back up data to external optical discs using a DVD or Blu-ray writer
- Repurpose your spare slim SATA optical drive into a portable USB 3.0 optical drive

Features

- Increase the capabilities of your computer by adding external support for a DVD or Blu-ray ROM drive
- Protect your optical disc drive with a solid aluminum housing
- Maximize portability with this USB powered device
- Enjoy plug-and-play installation with no software or driver disc required
- Save time accessing files with USB 3.0 performance


Hardware

Warranty	2 Years
Interface	USB 3.0
Bus Type	USB 3.0
Number of Drives	1
Drive Size	5.25in
Compatible Drive Types	Slimline SATA
Drive Installation	Fixed
Supported Drive Height(s)	12.7mm
Chipset ID	Initio - INIC-3619

Performance

Maximum Data Transfer Rate	5 Gbps
Type and Rate	USB 3.0 - 5 Gbit/s
UASP Support	No
Type and Rate	SATA II (3 Gbps)
Hot Swap Capability	Yes
General Specifications	Supports Blu-ray, CD or DVD-ROM drives

Connector(s)



Drive Connectors	Slimline SATA (13 pin, Data & Power)
Host Connectors	USB 3.0 Micro-B (10 pin, SuperSpeed)

Software

OS Compatibility	OS independent; No software or drivers required
------------------	---

Special Notes / Requirements

Note	Some USB hosts may not provide enough power to operate the enclosure with an installed ODD from a single USB port. A USB Y-cable may be required to power the drive.
------	--

Power

Power Source	USB-Powered
--------------	-------------

Environmental

Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-20C to 70C (-4F to 158F)
Humidity	10~90% RH

Physical Characteristics

Color	Black
Material	Aluminum and Plastic
Max Drive Height	0.7 in [17.5 mm]
Product Length	5.9 in [15 cm]
Product Width	5.4 in [13.6 cm]
Product Height	0.8 in [20 mm]
Weight of Product	9.2 oz [260 g]

Packaging Information

Package Length	5.9 in [15.1 cm]
Package Width	8.2 in [20.8 cm]
Package Height	1.7 in [44 mm]
Shipping (Package)	14.1 oz [399 g]



Weight

**What's in the
Box**

Included in Package	USB 3.0 to Slimline SATA ODD Enclosure
	USB 3.0 cable
	Installation screw kit
	Quick Start Guide

****Product appearance and specifications are subject to change without notice.***

