

7m Fiber Optic Cable - Single-Mode Duplex 9/125 LSZH Fiber Jumper Cord - LC/LC

Produkt ID: SMFIBLCLC7



The SMFIBLCLC7 7m LC to LC Single-Mode Duplex Fiber Cable features 9/125 micron fiber for high-speed, high bandwidth data transmissions over Gigabit Ethernet and Fiber Channel networks, with support for duplex single-mode applications.

This LC-LC patch cable is housed in a LSZH (Low-Smoke, Zero-Halogen) flame retardant jacket, to ensure minimal smoke, toxicity and corrosion when exposed to high sources of heat, in the event of a fire – an ideal solution for use in industrial settings, central offices and schools, as well as residential settings where building codes are a consideration.

Each Duplex 9/125 (OS1) Single-Mode Fiber Patch Cable is individually tested and certified to be within acceptable optical insertion loss limits for guaranteed compatibility and 100% reliability, and is backed by our lifetime warranty.

Certifikat, rapporter och kompatibilitet



Användning

- Use in Gigabit Ethernet and Fiber Channel applications
- Ideal solution for data applications requiring high speed data transmission
- Broadband systems

- Telecommunication/Data communication
- Fiber Connections in Patch Panels, Hubs, Switches, Routers

Funktioner

- 2x LC SM male connectors
- OS1 (9/125)
- LSZH (Low-Smoke, Zero-Halogen) cable jacket
- Attenuation loss meets or exceeds industry standards
- Molded connectors

Hårdvara

Garantipolicy	Lifetime
Fiberstorlek	9/125
Brandteknisk klass	LSZH-klassad (Low Smoke Zero Halogen)
Fiberklassificering	OS1

Prestanda

Maximal dataöverföringshastighet	10 Gbps
Kabelklassificering	1Gbps / 10Gbps
Fibertyp	Enkelläge

Kontakt(er)

Connector A	1 - Fiberoptisk LC duplex
Connector B	1 - Fiberoptisk LC duplex

Miljö

Drifttemperatur	-20°C to 60°C (-4°F to 140°F)
Förvaringstemperatur	-20°C to 60°C (-4°F to 140°F)

	Luftfuktighet	0~90% RH
Utseende		
	Färg	Gul
	Kabellängd	23.0 ft [7 m]
	Produktlängd	23.0 ft [7.0 m]
	Produktbredd	0.0 in [0.0 cm]
	Produkthöjd	0.0 in [0.0 cm]
	Produktvikt	3.3 oz [94.0 g]
Förpackning		
	Förpackningsantal	1
	Paketets längd	6.4 in [16.3 cm]
	Paketets bredd	7.7 in [19.5 cm]
	Paketets höjd	1.3 in [3.3 cm]
	Fraktvikt (förpackning)	3.3 oz [94.0 g]
Vad det är i lådan		
	Ingår i paketet	1 - 7m Single Mode Duplex Fiber Patch Cable LC-LC
Warranty Information		
	Warranty	Livslängd

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.