


Fiber Optic Cable - Single-Mode Duplex 9/125 - LSZH - LC/SC - 4 m

Produkt ID: SMFIBLCSC4



The SMFIBLCSC4 4m LC to SC Single-Mode Duplex Fiber Cable features 9/125 micron fiber for high-speed, high bandwidth data transmissions over Gigabit Ethernet and Fiber Channel networks, with support for duplex single-mode applications.

This LC-SC patch cable is housed in a LSZH (Low-Smoke, Zero-Halogen) flame retardant jacket, to ensure minimal smoke, toxicity and corrosion when exposed to high sources of heat, in the event of a fire – an ideal solution for use in industrial settings, central offices and schools, as well as residential settings where building codes are a consideration.

Each Duplex 9/125 (OS1) Single-Mode Fiber Patch Cable is individually tested and certified to be within acceptable optical insertion loss limits for guaranteed compatibility and 100% reliability, and is backed by our lifetime warranty.

Certifikat, rapporter och kompatibilitet

Användning

- Use in Gigabit Ethernet and Fiber Channel applications
- Ideal solution for data applications requiring high speed data transmission
- Broadband systems
- Telecommunication/Data communication
- Fiber Connections in Patch Panels, Hubs, Switches, Routers

Funktioner

- 1x LC SM male connector
- 1x SC SM male connector
- OS1 (9/125)
- LSZH (Low-Smoke, Zero-Halogen) cable jacket
- Attenuation loss meets or exceeds industry standards
- Molded connectors

Hårdvara

Garantipolicy	Lifetime
Brandteknisk klass	LSZH-klassad (Low Smoke Zero Halogen)
Fiberstorlek	9/125

Prestanda

Maximal dataöverföringshastighet	100Gbps
Kabelklassificering	10Gbps / 40Gbps / 100Gbps
Fiberklassificering	OS1
Fibertyp	Enkelläge

Kontakt(er)

Connector A	Fiberoptisk LC duplex
Connector B	Fiberoptisk SC duplex

Miljö

Drifttemperatur	-20°C to 60°C (-4°F to 140°F)
Förvaringstemperatur	-20°C to 60°C (-4°F to 140°F)
Luftfuktighet	0~90% RH

Utseende

Färg	Gul
Kabellängd	13.1 ft [4 m]
Produktlängd	13.1 ft [4 m]
Produktvikt	2.3 oz [64 g]

Förpackning

Förpackningsantal	1
Package Length	8.3 in [21 cm]
Package Width	7.5 in [19 cm]
Package Height	0.8 in [20 mm]
Fraktvikt (förpackning)	2.6 oz [74 g]

Vad det är i lådan

Ingår i paketet	4m Single Mode Duplex Fiber Patch Cable LC-SC
-----------------	---

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

