

VGA over Cat 5 UTP Video Extender Repeater

Product ID: ST121EXTEU



The ST121EXTEU VGA over Cat 5 UTP Video Extender Repeater allows you to further extend your VGA signal over Cat5 or better cabling. This device is specially designed for use with the StarTech.com ST121 VGA Video over Cat 5 extender series, which is comprised of a transmitter unit (ST1214TEU or ST121UTPEU) and an ST121REU receiver unit.

The ST121EXTEU VGA extender repeater adds to the overall extension distance capability, for a total of 300 meters (1000 feet) between the transmitter and receiver unit and also features a VGA output allowing you to connect an additional display at the mid-point of your setup.

For even more versatility, up to three ST121EXTEU repeater units can be used between the transmitter and receiver units, allowing monitors to be connected at each repeater station while further extending the overall connection distance by 150 meters (492 feet) per repeater used.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Place the display in a convenient viewing area, while the system equipment is placed elsewhere in a clean and secure environment
- Ideal for digital signage applications in financial, educational, and business sectors
- Extend your display across harsh environment industrial sites
- Perfect for video conferencing solutions in boardrooms and office settings

- Optimize placement of your demo stations at tradeshow and in auditoriums

Features

- Acts as repeater to add 820 feet to total extension distances provided by ST121UTPEU and ST1214TEU
- Extends video cables by up to 500 ft. (150m)
- Provides additional display/drop points for existing Cat5 signal extensions
- Pure hardware design, no software or drivers required
- Supports VGA, SVGA, and Multisync monitors
- Provides crystal clear picture quality

Hardware

Warranty	2 Years
Ports	1
Cabling	Cat 5 UTP
Daisy-Chain	Yes

Performance

Maximum Cable Length	500.0 ft [152.4 m]
Max Distance	150 m / 500 ft
Maximum Analog Resolutions	1024 x 768 @ 500 feet (150m)

Connector(s)

Remote Unit Connectors	RJ-45
	VGA (15 pin, High Density D-Sub)

Power

Power Source	AC Adapter Included
Input Voltage	230 AC
Output Voltage	9V DC
Output Current	0.6A



Center Tip Polarity	Positive
Plug Type	M

Physical Characteristics

Color	Black
Material	Aluminum
Product Length	4.1 in [10.3 cm]
Product Width	2.5 in [64.0 mm]
Product Height	0.8 in [20.6 mm]
Weight of Product	7.2 oz [204 g]

Packaging Information

Package Length	8.7 in [22 cm]
Package Width	4.1 in [10.4 cm]
Package Height	3.9 in [98 mm]
Shipping (Package) Weight	22.2 oz [630.0 g]

What's in the Box

Included in Package	REMOTE UNIT VGA EXTENDER
	9V AC 500ma ADAPTERS
	INSTRUCTION MANUAL

**Product appearance and specifications are subject to change without notice.*

