

SPDIF Digital Coaxial or Toslink Optical to Stereo RCA Audio Converter

Product ID: SPDIF2AA



The SPDIF2AA Toslink/Optical SPDIF to RCA Audio Converter lets you convert a 2-channel Digital Coaxial or Toslink/Optical SPDIF input signal into an RCA analog stereo output.

Perfect for home and professional audio applications, this SPDIF to RCA audio converter saves the cost of upgrading equipment for compatible connections, and offers separate Digital Coax and Toslink inputs for dual-function conversion. The small form factor design makes it suitable for installation into virtually any location, regardless of space constraints, while still providing a lossless audio signal. Plus, the digital coaxial or Toslink to RCA converter supports plug-and-play installation, saving you time and hassle.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Connect newer Blu-Ray, DVD Players and Game Consoles to two channel analog stereo receivers
- Convert or extend your digital audio input into an analog format, without signal or quality loss

Features

- Compact form factor
- Easy to install and use
- Accepts Digital Coax or Toslink digital audio input

- Outputs analog L/R RCA stereo analog audio
- 24-bit S/PDIF incoming bit stream
- Supports 32, 44.1, 48 and 96 KHz sampling rates

Hardware

Warranty	2 Years
AV Input	Digital Coaxial Toslink
AV Output	RCA Audio

Performance

Audio Specifications	2 channel (stereo) supported 32, 44.1, 48 and 96 KHz Sampling rates
----------------------	--

Connector(s)

Connector A	Toslink (SPDIF, Optical) Digital Coax Audio (RCA)
Connector B	Stereo Audio (2 x RCA)

Power

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	0.5 A
Output Voltage	5 DC
Output Current	2.0 A
Center Tip Polarity	Positive
Plug Type	N
Power Consumption (In Watts)	0.5

Environmental

Operating Temperature	0C to 70C (32F to 158F)
-----------------------	-------------------------



Storage Temperature	-10C to 80C (14F to 176F)
Humidity	10~85 % RH Non-Condensing

Physical Characteristics

Color	Black
Material	Steel
Product Length	2.0 in [52 mm]
Product Width	1.7 in [42 mm]
Product Height	1.1 in [27 mm]
Weight of Product	2.5 oz [72 g]

Packaging Information

Package Length	6.7 in [17 cm]
Package Width	4.7 in [12 cm]
Package Height	2.3 in [58 mm]
Shipping (Package) Weight	13.0 oz [368 g]

What's in the Box

Included in Package	SPDIF to RCA converter
	universal power adapter (NA, EU, UK, ANZ)
	instruction manual

****Product appearance and specifications are subject to change without notice.***

