

Docking Station Mount - VESA Compatible - Steel - TAA

Product ID: SSPMSVESA



Create a clutter-free workspace by mounting your docking station or hub, freeing up space on your desktop. This VESA compatible docking station mount makes it easy to attach a compatible StarTech.com dock or hub to the backside of your monitor.

The docking station mounting plate attaches easily to monitors with a 75x75 or 100x100 mm VESA hole pattern.

Made in Canada, the sturdy and durable dock and hub mount is engineered from 10 gauge steel (3.3 mm thick).

The VESA docking station and hub mount works with monitors mounted on a stand, or attached to a monitor arm. The docking station mount provides a great way to free up desk space in offices in business or commercial spaces. It's also ideal for space-constrained areas, including hot desks and shared workstations, cubicles, mobile and wall-mounted workstations, and home offices.

This innovative mount is designed to work exclusively with compatible StarTech.com products including:

4-Port USB-C 10Gbps Hub - USB 3.1 to 3x USB-A + 1x USB-C (HB31C3A1CS)

4-Port USB-C 10Gbps Hub - USB 3.1 to 4x USB-A - Self Powered (HB31C4AS)

3-Port USB-C Hub with GbE - USB 3.1 (10Gbps) (HB31C2A1CGS)

USB-C & USB-A 5Gbps Docking Station - USB 3.1 (5Gbps) Universal Laptop Docking Station (DK30C2DPPDUE - UK/EU)

Thunderbolt 3 Dual Monitor Docking Station - Thunderbolt 3 w/ USB-C compatibility - Dual Monitor 4K60Hz (TB3CDK2DPUE - UK/EU)

USB-C 3.1 5Gbps Dual Monitor Docking Station - USB-C 3.1 Gen 1 - Dual Monitor 1080p (DK30CHHPDUK - UK only)

USB-C & USB-A 5Gbps Docking Station - USB 3.1 (5Gbps) Universal Laptop Docking Station (DK30C2DPPD)

Thunderbolt 3 Dual Monitor Docking Station - Thunderbolt 3 w/ USB-C compatibility - Dual Monitor 4K60Hz (TB3CDK2DP)

USB-C 3.1 5Gbps Dual Monitor Docking Station - USB-C 3.1 Gen 1 - Dual Monitor 1080p (DK30CHHPDEU - EU only)

USB-C 3.1 5Gbps Dual Monitor Docking Station - USB-C 3.1 Gen 1 - Dual Monitor 1080p (DK30CHHPDAU - AU only)

USB-C 3.1 5Gbps Dual Monitor Docking Station - USB-C 3.1 Gen 1 - Dual Monitor 1080p (DK30CHHPD)

Thunderbolt 3 10Gbps Dual Monitor Docking Station - Thunderbolt 3.1 - USB-C 3.1 Gen 2 - Dual Monitor 4K (TB3CDK2DH)

Thunderbolt 3 10Gbps Dual Monitor Docking Station - Thunderbolt 3.1 - USB-C 3.1 Gen 2 - Dual Monitor 4K (TB3CDK2DHUE - UK/EU)

USB-C 3.1 10Gbps Triple Monitor Docking Station - USB-C 3.1 Gen 2 - Triple Monitor 4K (DK31C3HDPD)

USB-C 3.1 10Gbps Triple Monitor Docking Station - USB-C 3.1 Gen 2 - Triple Monitor 4K (DK31C3HDPD - UK/EU)

USB-C 3.1 10Gbps Quad Monitor Docking Station - USB-C 3.1 Gen 2 - Quad Monitor 4K (DK31C4DPPD).

Using the docking station mounting kit, complete with mounting plate and screws, you can mount your compatible dock or hub to the back of your monitor that is recessed up to 7mm. When installed, the dock mount sits almost flush with the monitor, while still allowing easy access.

SSPMSVESA is backed by a StarTech.com 5-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Ideal for offices in business or commercial spaces, where the back of the monitor is not customer-facing
- Create more desk space in space-constrained areas, including hot desks, cubicles and home offices

Features

- Save space by mounting your StarTech.com docking station or hub to the back of your VESA compatible monitor
- Attaches to the back of monitors with a VESA 75x75 or 100x100 mm hole pattern
- Robust construction made of strong 10 gauge steel (3.3 mm thick)

- Docking station and hub mounting kit includes VESA mounting plate and screws
- TAA compliant

Hardware

Warranty	5 Years
Mounting Options	Back of Monitor, Under Desktop, or Clamped to Monitor-Mount Pole
VESA Hole Pattern(s)	75x75 mm 100x100 mm

Special Notes / Requirements

Note	When mounting the adapter (recessed): the screws and spacers provided will allow you to mount to a VESA pattern on the back of the monitor that is recessed, to a maximum of 7 mm. If the recessed area is deeper than 7 mm, you will need to use longer screws than those provided.
------	--

Physical Characteristics

Color	Black
Material	Steel
Product Length	8.4 in [21.4 cm]
Product Width	4.7 in [12.0 cm]
Product Height	0.1 in [0.3 cm]
Weight of Product	1.2 lb [0.5 kg]

Packaging Information

Package Quantity	1
Package Length	8.9 in [22.6 cm]
Package Width	5.7 in [14.4 cm]
Package Height	0.9 in [2.3 cm]
Shipping (Package) Weight	1.2 lb [0.6 kg]

What's in the Box

Included in Package	1 - VESA Mounting Bracket
	4 - M3-0.5 x 5 mm Countersunk Screws
	4 - M4 x 12 mm Screws
	4 - M4 x 20 mm Screws
	4 - Plastic Spacers
	1 - Quick-Start Guide

****Product appearance and specifications are subject to change without notice.***