

## VGA over Cat5 Video Extender Receiver

Produkt ID: ST121REU



The ST121REU VGA over Cat5 Video Extender Receiver is specifically designed for use as the receiver unit for the ST121 VGA over Cat5 UTP Extender transmitter series allowing you to split and extend a single VGA source to up to eight remote displays.

From the transmitter device, the VGA video signal is sent over standard 4 pair Category 5 or better UTP cable to remote monitors, each connected to an ST121REU Cat 5 VGA receiver - supporting distances of up to 150 meters (500 feet).

A cost-effective video extension solution, this receiver is ideal for a wide range of environments including airports, bus depots, retail, or any large buildings where VGA video needs to be extended to long connection distances.

This product is TAA compliant and backed by a Startech.com 2-year warranty with free lifetime technical support.

## Certifikat, rapporter och kompatibilitet

### Användning

- Place the display in a convenient viewing area, while the system equipment is placed elsewhere in a clean and secure environment
- Ideal for digital signage applications in financial, educational, and business sectors
- Extend your display across harsh environment industrial sites

- Perfect for video conferencing solutions in boardrooms and office settings
- Optimize placement of your demo stations at tradeshows and in auditoriums

## Funktioner

- Extends video cables by up to 500 ft. (150m)
- Supports 1024x768 resolution at 150 ft. (50m)
- Pure hardware design, no software or drivers required
- Uses standard Cat 5 or better cabling
- Supports VGA, SVGA, and Multisync monitors
- Provides crystal clear picture quality

---

### Hårdvara

Garantipolicy	2 Years
Portar	1
Kablage	Cat 5 UTP
Kedjekoppling	Ja

---

### Prestanda

Maximal kabellängd	499.9 ft [152.4 m]
Maximalt avstånd	150 m / 500 ft
Maximal analog upplösning	1024 x 768 @ 500 feet (150m)

---

### Kontakt(er)

Fjärrenhetskontakter	RJ-45
	VGA (15-stifts, High Density D-Sub)

---

### Ström

Power Source	AC-adapter medföljer
Inspänning	100 - 240 AC



Inström	0.2
Utspanning	12V DC
Utström	0.5A
Polaritet på mittpol	Positiv
Kontakttyp	M
Strömförbrukning	6

---

#### Utseende

Färg	Svart
Kabinettyp	Aluminium
Produktlängd	3.3 in [84.2 mm]
Produktbredd	2.6 in [65.1 mm]
Produkthöjd	0.8 in [20.6 mm]
Produktvikt	6.0 oz [171.0 g]

---

#### Förpackning

Package Length	8.7 in [22.0 cm]
Package Width	3.9 in [100.0 mm]
Package Height	3.9 in [100.0 mm]
Fraktvikt (förpackning)	21.2 oz [600.0 g]

---

#### Vad det är i lådan

Ingår i paketet	REMOTE UNIT VGA EXTENDER
	9V AC 500ma ADAPTORS
	INSTRUCTION MANUAL

---

\* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

