

## 4 Port VGA Video Splitter - 250 MHz

**Product ID:** ST124LGB



The ST124LGB 4 Port VGA Video Splitter allows a single VGA source to display VGA video onto four monitors simultaneously. Perfect for classrooms, tradeshow, or in-store displays where high quality video on several monitors is needed. The simple plug and play operation makes setup quick and easy so you can be up and running in minutes.

The ST124LGB supports up to 250 MHz of video bandwidth, providing brilliant resolutions up to 1920x1440. A built-in booster circuit lets you situate your displays up to 210 ft away from your source.

Backed by a StarTech.com 2-year warranty and free lifetime technical support. Male to Female VGA extension cable required (MXT101HQ)

## Certifications, Reports and Compatibility

### Applications

- Use for in-store product merchandising in retail environments to give your advertisements greater visibility
- Display travel schedules and alerts in airports, bus terminals and train stations
- Create engaging multimedia presentations for demonstration in lecture halls and classrooms
- Get your message across multiple displays for trade-shows or information booths/kiosks
- Quick and easy solution to split a video signal in an auditorium or house of worship

### Features

- Supports resolutions up to 1920x1440

- Supports cable distances up to 210ft
- 250MHz video bandwidth
- Supports Cascading up to 3 levels
- Compatible with VGA, SVGA and Multisync monitors

---

#### Hardware

Warranty	2 Years
Ports	4

---

#### Performance

Maximum Cable Length	213.2 ft [65 m]
Maximum Analog Resolutions	1920x1440
Bandwidth	250MHz
General Specifications	Male to Female VGA extension cable required (MXT101HQ)

---

#### Connector(s)

Connector Type(s)	VGA (15 pin, High Density D-Sub)
	VGA (15 pin, High Density D-Sub)

---

#### Power

Power Source	AC Adapter Included
Output Voltage	9V DC
Output Current	0.5A

---

#### Physical Characteristics

Color	Black
Material	Steel
Product Length	8.1 in [20.7 cm]
Product Width	2.8 in [70 mm]
Product Height	1.0 in [26 mm]



Weight of Product	14.8 oz [419.6 g]
-------------------	-------------------

---

**Packaging Information**

Package Length	10.8 in [27.4 cm]
----------------	-------------------

Package Width	3.2 in [81 mm]
---------------	----------------

Package Height	7.5 in [19 cm]
----------------	----------------

Shipping (Package) Weight	34.2 oz [970 g]
---------------------------	-----------------

---

**What's in the Box**

Included in Package	4 Port VGA Splitter
---------------------	---------------------

	Power Adapter
--	---------------

	User Manual
--	-------------

---

***\*Product appearance and specifications are subject to change without notice.***

