

4 Port VGA Video Extender over Cat 5 (UTPE Series)

Product ID: ST124UTPE



The ST124UTPE 4 Port VGA Video Extender over Cat 5 (UTPE Series) allows up to 5 (1 local and 4 remote) monitors to be connected to a single VGA source.

The video signal is carried to the remote monitors over standard 4 pair Category 5 and Category 6 UTP cable using RJ45 connectors and supports distances of up to 300m / 950ft.

At each remote monitor an STUTPRXL receiver (see accessories) is required. The receiver unit converts the signal from the UTP cable back into VGA video for the monitor.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Digital Signage

Certifications, Reports and Compatibility

Applications

- Use digital signage to catch the attention of your audience and deliver up to date content the way you want it to be seen and heard
- Place the display in a convenient viewing area, while the system equipment is placed elsewhere in a clean and secure environment
- Ideal for digital signage applications in financial, educational, and business sectors

Features

- Monitor receivers are sold separately (See STUTPRXL)
- Simultaneously displays the same image on 4 monitors
- Supports a maximum resolution of 1920x1200
- Cascadable up to three levels

Hardware

Warranty	2 Years
Ports	4
Cabling	Cat 5 UTP or better
Audio	No
Daisy-Chain	Yes

Performance

Max Distance	300 m / 950 ft
Supported Resolutions	1920x1200 @ 50m(150ft) 1600x1200 @ 100m(300ft) 1280x1024 @ 180m(550ft) 1024x768 @ 200m(620ft) 800x600 @ 300m(950ft)

Connector(s)

Local Unit Connectors	VGA (15 pin, High Density D-Sub) RJ-45
-----------------------	---

Special Notes / Requirements

System and Cable Requirements	One STUTPRXL standalone, or STUTPRXWAL wall-plate receiver unit per display that you are connecting
-------------------------------	---

Power

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC



Output Voltage	12V DC
Output Current	0.6A
Plug Type	M
Power Consumption (In Watts)	7.2

Physical Characteristics

Color	Black
Material	Steel
Product Length	3.3 in [83.5 mm]
Product Width	5.1 in [13 cm]
Product Height	1.2 in [29.5 mm]
Weight of Product	8.7 oz [247 g]

Packaging Information

Package Length	8.9 in [22.6 cm]
Package Width	2.6 in [67 mm]
Package Height	7.4 in [18.9 cm]
Shipping (Package) Weight	31.4 oz [890 g]

What's in the Box

Included in Package	Instruction Manual
	UTP Video Splitter Base Unit
	Power Adapter
	6ft (1.8m) VGA Cable

****Product appearance and specifications are subject to change without notice.***

