

## 8 Port VGA Video Extender over Cat 5 (UTPE Series)

**Product ID:** ST128UTPE



The ST128UTPE 8 Port VGA Video Extender over Cat 5 (UTPE Series) allows up to 9 (1 local and 8 remote) monitors to be connected to a single VGA source.

The video signal is carried to the remote monitors over standard 4 pair Category 5 and Category 6 UTP cable using RJ45 connectors and supports distances of up to 300m / 950ft.

At each remote monitor an STUTPRXL receiver (see accessories) is required. The receiver unit converts the signal from the UTP cable back into VGA video for the monitor.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Digital Signage

## Certifications, Reports and Compatibility

### Applications

- Ideal for digital signage applications in financial, educational, and business sectors
- Place the display in a convenient viewing area, while the system equipment is placed elsewhere in a clean and secure environment
- Use digital signage to catch the attention of your audience and deliver up to date content the way you want it to be seen and heard

### Features

- Simultaneously displays the same image on 8 monitors
- Supports a maximum resolution of 1280 x 1024 @ 60 Hz refresh rate
- Monitor receivers are sold separately (See STUTPRXL)
- Monitors can be up to 300m / 950ft away
- Cascadable up to three levels

---

#### Hardware

Warranty	2 Years
Ports	8
Cabling	Cat 5 UTP or better
Audio	No
Daisy-Chain	Yes

---

#### Performance

Max Distance	300 m / 950 ft
Maximum Analog Resolutions	1280 x 1024

---

#### Connector(s)

Local Unit Connectors	RJ-45
	VGA (15 pin, High Density D-Sub)

---

#### Special Notes / Requirements

System and Cable Requirements	One <a class="FeatureNavLink" href="http://www.startech.com/item/STUTPRXL">STUTPRXL</a> receiver unit per display that you are connecting
-------------------------------	---

---

#### Power

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Output Voltage	12V DC
Output Current	0.6A
Power Consumption (In	7.2



Watts)

---

**Physical Characteristics**

Color	Black
Material	Aluminum
Product Length	3.3 in [83.5 mm]
Product Width	7.9 in [20 cm]
Product Height	1.2 in [29.5 mm]
Weight of Product	8.7 oz [247 g]

---

**Packaging Information**

Package Length	11.7 in [29.8 cm]
Package Width	2.6 in [65 mm]
Package Height	7.5 in [19 cm]
Shipping (Package) Weight	2.3 lb [1.0 kg]

---

**What's in the Box**

Included in Package	UTP Video Splitter Base Unit
	6ft (1.8m) VGA Cable
	Universal Power Adapter (NA/UK/EU/AUS)
	Instruction Manual

---

*\*Product appearance and specifications are subject to change without notice.*

