

4 Port Compact Black USB 2.0 Hub - TAA

Produkt-ID: ST4202USB



This TAA compliant 4 Port USB 2.0 Hub connects to one USB 2.0 port on a Mac or PC computer, adding four USB 2.0 ports - allowing you to maximize the number of high speed USB peripherals connected to your computer. The hub supports cascaded installation with other USB 2.0 hubs, supporting up to 127 USB 2.0 device connections - a scalable solution for connecting multiple USB devices to a single host computer.

The 4 port hub includes a power adapter, but can be powered through USB bus connection to the host computer - allowing you to install the hub as needed without worrying about the availability of a power outlet.

The USB 2.0 hub offers an attractive black casing that suits any operating environment and includes a 3ft USB 2.0 A/B male-male cable, for the connection between the hub and the host computer.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Charge older portable devices like iPod's. The product is not suitable for charging modern

smartphones or tablets.

- Add additional USB 2.0 ports to a computer to connect more devices
- Move USB ports further away from the computer chassis with an external hub
- Make hard to reach USB ports more accessible, by being able to position the hub anywhere the cable will reach

Merkmale

- TAA Compliant
- High Speed USB 2.0 compliant, with supported data transfer rates up to 480 Mbps
- Backwards compatible with USB 1.1/1.0 devices
- Includes optional external power adapter
- Compact and light-weight design
- Plug and Play and Hot Swap compatible

Hardware

Garantiebestimmungen	2 Years
Ports	4
Schnittstelle	USB 2.0
Industrienormen	USB 2.0
Chipset-ID	Genesys Logic - GL850G

Leistung

Max. Datenübertragungsrate	480 Mbps
MTBF	75,537 hours

Steckverbinder

Externe Ports	4 - USB 2.0 Typ-A (4 pin, 480Mbit/s)
	1 - USB B (4-polig)

Software

Betriebssystemkompatibilität	OS Independent; No software or drivers required. (For Apple, Mac OS 10.2.4 needed for USB 2.0 speeds)
------------------------------	---

Spezielle Hinweise/Anforderungen

System- und Kabelanforderungen	Any computer with a USB 2.0 port
--------------------------------	----------------------------------

Strom

Stromversorgung	Mit Netzadapter
Eingangsspannung	100 - 240 AC
Eingangsstrom	0.35 A
Ausgangsspannung	5 DC
Ausgangsstrom	2A
Polarität der Mittelspitze	Positiv
Steckertyp	H
Stromverbrauch	10

Umgebungsbedingungen

Betriebstemperatur	0 to 70 Degrees °C
--------------------	--------------------

Physische Eigenschaften

Farbe	Schwarz
Gehäusetyp	Kunststoff
Produktlänge	23.6 in [60 cm]
Produktbreite	3.9 in [10 cm]
Produkthöhe	0.8 in [2.0 cm]
Produktgewicht	2.5 oz [71.0 g]

Verpackungsinform

ationen

Paketmenge	1
Paketlänge	8.3 in [21.0 cm]
Paketbreite	5.7 in [14.5 cm]
Pakethöhe	1.6 in [4.0 cm]
Versandgewicht (Verpackung)	9.7 oz [276.0 g]

Verpackungsinhalt

Im Paket enthalten	1 - 4 Port USB 2.0 Hub
	1 - USB Cable
	1 - Power Adapter
	1 - Instruction Manual

Garantieinformationen

Warranty	2 Jahre
----------	---------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.