

4-Port USB-A Hub, 5Gbps, Self-Powered, 2-in-1 USB-C and USB-A Host Cable, 1x BC 1.2 Charging Port, 24W Power Adapter Included, MacBook and Windows

**Product ID:** ST4300USB3V2-UE



This 4port SuperSpeed USB hub lets you instantly add four USB-A 3.0 ports, including one BC 1.2 charging port, from a single USB connection-ideal for connecting keyboards, mice, flash drives, and external storage devices at the same time.

The dedicated BC 1.2 fastcharge port delivers up to 1.5A (7.5W) and supports CDP for data and charging or DCP for charging when the hub isn't connected to a computer. A 24W total power budget is shared across all ports for reliable device charging.

Powered by the included 24W external adapter, the selfpowered hub ensures stable performance even with multiple devices connected. Builtin overcurrent and overvoltage protection helps reduce device dropouts and protects the host system, while support for Wake on USB and USB event monitoring enhances manageability.

A removable 2in1 USBC/USBA host cable provides flexible connectivity with modern and legacy systems.

The hub features a 70% postconsumer recycled (PCR) plastic enclosure and a 35% PCR TPE jacket, helping reduce environmental impact and support ESG requirements.

## Certifications, Reports and Compatibility



OperatingSystem  
Independent

## Applications

## Features

- **Plug-and-Play USB Connectivity:** Instantly add four SuperSpeed USB-A 3.0 ports, including one BC 1.2 charging port, from a single USB connection; Ideal for connecting keyboards, mice, flash drives, and external storage devices simultaneously
- **Fast Charge, Even Without a Host:** Deliver up to 1.5A (7.5W) from a BC 1.2 fast-charge port that supports CDP for data and charge, or DCP for charging when the hub isn't connected to a computer; 24W total power budget is shared across all ports
- **Power Devices Reliably with Included 24W Adapter:** Self-powered hub ensures stable charging and operation with built-in overcurrent and overvoltage protection to reduce device dropout and host shutdown risk; Supports Wake on USB and USB event monitoring
- **Designed for Easy Access and Flexible Setup:** Single-face port layout streamlines cable management, while the removable 2-in-1 USB-C/USB-A host cable supports stable connectivity across modern and legacy systems
- **The IT Pro's Choice:** Our USB hubs are rigorously tested in our Innovation Lab to ensure enterprise-grade reliability and cross-platform compatibility; Built to support large-scale deployments and expanding peripheral connectivity in modern IT environments

### General

|          |              |
|----------|--------------|
| UPC      | 065030925051 |
| Warranty | 2 Years      |

### Special Notes / Requirements

|               |                                                               |
|---------------|---------------------------------------------------------------|
| Special Notes | USB 3.2 Gen 1 (5Gbps) is also known as USB 3.1 Gen 1 (5Gbps). |
|---------------|---------------------------------------------------------------|

### Power

|                     |                     |
|---------------------|---------------------|
| Power Source        | AC Adapter Included |
| Input Voltage       | 100 - 240 AC        |
| Input Current       | 700mA               |
| Output Voltage      | 12V DC              |
| Output Current      | 2                   |
| Center Tip Polarity | Positive            |
| Plug Type           | M                   |

Power Consumption 24W

#### Physical & Environmental

|                       |                           |
|-----------------------|---------------------------|
| Color                 | Black                     |
| Material              | 70% PCR Plastic           |
| Cable Length          | 3.3 ft [1 m]              |
| Product Length        | 4.0 in [10.1 cm]          |
| Product Width         | 2.0 in [52 mm]            |
| Product Height        | 0.6 in [16.5 mm]          |
| Weight of Product     | 2.0 oz [55.9 g]           |
| Operating Temperature | 0C to 40C (32F to 104F)   |
| Storage Temperature   | -20C to 60C (-4F to 140F) |
| Humidity              | 90% RH                    |

#### Performance

|                            |                        |
|----------------------------|------------------------|
| Maximum Data Transfer Rate | 5 Gbps (USB 3.2 Gen 1) |
| Type and Rate              | USB 5Gbps              |
| UASP Support               | Yes                    |
| MTBF                       | 117452 hours           |

#### Hardware

|                       |                                |
|-----------------------|--------------------------------|
| USB-C Host Connection | Yes                            |
| Fast-Charge Port(s)   | Yes                            |
| Number of Ports       | 4                              |
| Cable Jacket Material | TPE - Thermoplastic Elastomers |
| Interface             | USB 3.2 Gen 1 (5Gbps)          |
| Bus Type              | USB 3.2 Gen 1 (5 Gbps)         |
| Industry Standards    | USB 3.2 Gen 1 (5Gbps)          |

|                |                                                 |
|----------------|-------------------------------------------------|
| Chipset ID     | VIA - VL817S                                    |
| LED Indicators | 1 - Status LED:<br><br>Solid White: Power is On |
| Form Factor    | Desktop                                         |

---

#### Packaging & In-the-Box

|                           |                                                                                                                     |
|---------------------------|---------------------------------------------------------------------------------------------------------------------|
| Included in Package       | 1 - USB Hub<br><br>1 - Universal Power Adapter, UK/EU Clips<br><br>1 - USB-C Host Cable with USB-C to USB-A Adapter |
| Package Width             | 5.8 in [14.7 cm]                                                                                                    |
| Package Depth             | 7.9 in [20 cm]                                                                                                      |
| Package Height            | 1.9 in [49 mm]                                                                                                      |
| Shipping (Package) Weight | 12.0 oz [341.2 g]                                                                                                   |

---

#### Connector(s)

|                             |                     |
|-----------------------------|---------------------|
| Host Connector 1 (Quantity) | 1                   |
| Host Connector 1            | USB-C (5Gbps, 4.5W) |
| Connector 1 (Quantity)      | 3                   |
| Connector 1                 | USB-A (5Gbps, 4.5W) |
| Connector 2 (Quantity)      | 1                   |
| Connector 2                 | USB-A (5Gbps, 7.5W) |

---

***\*Product appearance and specifications are subject to change without notice.***