

7 Port Black USB 2.0 Hub - TAA

Productcode: ST7202USBGB



This TAA compliant 7 Port USB 2.0 Hub connects to one USB 2.0 port on a Mac or PC computer, adding seven USB 2.0 ports - allowing you to maximize the number of high speed USB peripherals connected to your computer. The hub supports cascaded installation with other USB 2.0 hubs, supporting up to 127 USB 2.0 device connections - a scalable solution for connecting multiple USB devices to a single host computer.

The 7 port hub includes a power adapter, but can be powered through USB bus connection to the host computer - allowing you to install the hub as needed without worrying about the availability of a power outlet.

The USB 2.0 hub offers an attractive black casing that suits any operating environment and includes a 3ft USB 2.0 A/B male-male cable, for the connection between the hub and the host computer.

Certificaties, rapporten en compatibiliteit



Toepassingen

- Connect digital cameras, keyboards, mice, MP3 players, scanners, printers, game pads, joysticks

and more to your laptop or desktop system

Eigenschappen

- TAA Compliant
- Backward compatible with USB 1.1 devices
- High-speed data transfer rates of up to 480 Mbits/sec
- Self-powered or bus-powered

Hardware

Garantiebeleid	2 Years
Poorten	7
Interface	USB 2.0

Prestaties

Maximale overdrachtsnelheid	480 Mbps
-----------------------------	----------

Connector(en)

Externe poorten	7 - USB 2.0 Type-A (4 pin, 480Mbps)
	1 - USB B (4-polig)

Software

Besturingssystemen	OS Independent; No additional drivers or software required
--------------------	--

Speciale opmerkingen / vereisten

Systeem- en kabelvereisten	1 x Free USB port
----------------------------	-------------------

Indicatoren

LED-indicatoren	1 - Power
-----------------	-----------

Voeding

Voedingsbron	Inclusief wisselstroomadapter
--------------	-------------------------------

Ingangsspanning	100 - 240 AC
Ingangsstroom	0.35 A
Uitgangsspanning	5 DC
Uitgangsstroom	2A
Polariteit pin midden	Positief
Stekkertype	H
Vermogensopname	10

Gebruiksomgeving

Bedrijfstemperatuur	0° C to 70° C
---------------------	---------------

Fysieke eigenschappen

Kleur	Zwart
Type behuizing	Kunststof
Lengte product	3.9 in [10.0 cm]
Breedte product	2.4 in [6.0 cm]
Hoogte product	0.8 in [2.0 cm]
Gewicht product	10.2 oz [290.0 g]

Verpakkingsinformatie

Verpakkingsaantal	1
Lengte Verpakking	8.5 in [21.5 cm]
Package Width	3.4 in [8.7 cm]
Package Height	2.0 in [5.2 cm]
Verzendgewicht (verpakt)	11.1 oz [315.0 g]

Wat wordt er meegeleverd

Meegeleverd	1 - 7 Port USB 2.0 Hub
-------------	------------------------

1 - USB 2.0 Cable

1 - Power Adapter

1 - Instruction Manual

Garantiebepalinge
n

Warranty

2 Jaar

* Uitvoering en specificaties van het product zijn zonder aankondiging vatbaar voor wijzigingen.