4-Port USB-A Hub, 5Gbps, Self-Powered, 2-in-1 USB-C and USB-A Host Cable, 1x BC 1.2 Charging Port, 24W Power Adapter Included, MacBook and Windows

Product ID: ST4300USB3V2-UE

,

This 4port SuperSpeed USB hub lets you instantly add four USBA 3.0 ports, including one BC 1.2 charging port, from a single USB connection-ideal for connecting keyboards, mice, flash drives, and external storage devices at the same time.

The dedicated BC 1.2 fastcharge port delivers up to 1.5A (7.5W) and supports CDP for data and charging or DCP for charging when the hub isn't connected to a computer. A 24W total power budget is shared across all ports for reliable device charging.

Powered by the included 24W external adapter, the selfpowered hub ensures stable performance even with multiple devices connected. Builtin overcurrent and overvoltage protection helps reduce device dropouts and protects the host system, while support for Wake on USB and USB event monitoring enhances manageability.

A removable 2in1 USBC/USBA host cable provides flexible connectivity with modern and legacy systems.

The hub features a 70% postconsumer recycled (PCR) plastic enclosure and a 35% PCR TPE jacket, helping reduce environmental impact and support ESG requirements.

Certifications, Reports and Compatibility

Applications

Features

• Plug-and-Play USB Connectivity: Instantly add four SuperSpeed USB-A 3.0 ports, including one BC 1.2 charging port, from a single USB connection; Ideal for connecting keyboards, mice, flash drives, and external storage devices simultaneously

• Fast Charge, Even Without a Host: Deliver up to 1.5A (7.5W) from a BC 1.2 fast-charge port that supports CDP for data and charge, or DCP for charging when the hub isn't connected to a computer; 24W total power budget is shared across all ports

• Power Devices Reliably with Included 24W Adapter: Self-powered hub ensures stable charging and operation with built-in overcurrent and overvoltage protection to reduce device dropout and host shutdown risk; Supports Wake on USB and USB event monitoring

• Designed for Easy Access and Flexible Setup: Single-face port layout streamlines cable management, while the removable 2-in-1 USB-C/USB-A host cable supports stable connectivity across modern and legacy systems

• The IT Pro's Choice: Our USB hubs are rigorously tested in our Innovation Lab to ensure enterprise-grade reliability and cross-platform compatibility; Built to support large-scale deployments and expanding peripheral connectivity in modern IT environments

General		
	UPC	065030925051
	Warranty	2 Years
Special Notes / Requirements		
	Special Notes	USB 3.2 Gen 1 (5Gbps) is also known as USB 3.1 Gen 1 (5Gbps).
Power		
	Power Source	AC Adapter Included
	Input Voltage	100 - 240 AC
	Input Current	700mA
	Output Voltage	12V DC
	Output Current	2 A
	Center Tip Polarity	Positive
	Plug Type	M

	Power Consumption	24W
Physical & Environmental		
	Color	Black
	Material	70% PCR Plastic
	Cable Length	3.3 ft [1 m]
	Product Length	4.0 in [10.1 cm]
	Product Width	2.0 in [52 mm]
	Product Height	0.6 in [16.5 mm]
	Weight of Product	2.0 oz [55.9 g]
	Operating Temperature	0C to 40C (32F to 104F)
	Storage Temperature	-20C to 60C (-4F to 140F)
	Humidity	90% RH
Performance		
	Maximum Data Transfer Rate	5 Gbps (USB 3.2 Gen 1)
	Type and Rate	USB 5Gbps
	UASP Support	Yes
	MTBF	117452 hours
Hardware		
	USB-C Host Connection	Yes
	Fast-Charge Port(s)	Yes
	Number of Ports	4
	Cable Jacket Material	TPE (Thermoplastic Elastomer)
	Interface	USB 3.2 Gen 1 (5Gbps)
	Bus Type	USB 5Gbps
	Industry Standards	USB 3.2 Gen 1 (5Gbps)

	Chipset ID	VIA - VL817S
	LED Indicators	1 - Status LED: Solid White: Power is On
	Form Factor	Desktop
Packaging & In-the-Box		
	Included in Package	1 - USB Hub 1 - Universal Power Adapter, UK/EU Clips 1 - USB-C Host Cable with USB-C to USB-A Adapter
	Package Width	5.8 in [14.7 cm]
	Package Depth	7.9 in [20 cm]
	Package Height	1.9 in [49 mm]
	Shipping (Package) Weight	12.0 oz [341.2 g]
Connector(s)		
	Host Connector 1 (Quantity)	1
	Host Connector 1	USB-C (5Gbps, 4.5W)
	Connector 1 (Quantity)	3
	Connector 1	USB-A (5Gbps, 4.5W)
	Connector 2 (Quantity)	1
	Connector 2	USB-A (5Gbps, 7.5W)

Product appearance and specifications are subject to change without notice.