

7-Port USB Charging Station with 5x 1A Ports and 2x 2A Ports

Produkt-ID: ST7C51224



Charge up to seven mobile devices simultaneously. This 7-port USB charging station lets you set up a multiport charge point for tablets, phones and other mobile devices.

This standalone USB charging strip offers five 1A and two 2A USB charging ports, so you can charge several mobile devices at the same time, without having to connect to multiple wall outlets or power bars.

The 7-port charging station supports Smart Charging capabilities, including USB Battery Charging Specification 1.2, and Apple and Samsung protocols, which ensures compatibility with a broad range of mobile devices, like the Apple iPhone and iPad, the Samsung Galaxy Tab, Android devices and more.

Create a dedicated USB charging station at your desk, so you can charge your mobile devices while you work. The charging station is also a great addition to your boardroom or lobby, providing a convenient way for mobile users to keep their devices powered.

With its integrated power button, you can turn all of the ports off while the charger isn't in use.

This compact charging strip takes up minimal space and features a rugged metal housing that can withstand the wear and tear of daily use. With the included wall-mount bracket, you can attach the charging strip to a surface such as a desktop or wall, for easy access to charge ports.

The StarTech.com ST7C51224 is backed by a 2-year warranty and free lifetime technical support.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Charge multiple devices simultaneously
- Ideal for boardrooms, lobbies, IT helpdesks and test benches
- Install in locations where the charging strip can be securely mounted

Merkmale

- Charge multiple devices simultaneously with five 1A ports and two 2A ports
- Free up wall outlets using a consolidated charging station
- Mount the charging strip to a desk or wall with the included mounting bracket
- Save space on your desk, work bench or conference table with the station's compact design
- Supports Smart Charging capabilities

Hardware

Garantiebestimmungen	2 Years
Ports	7
Industrienormen	USB Battery Charging Specification Rev. 1.2

Steckverbinder

Steckverbindertyp(en)	7 - USB 2.0 Typ-A (4 pin, 480Mbit/s)
-----------------------	--------------------------------------

Anzeiger

LED-Anzeiger	1 - Power
--------------	-----------

Strom

Stromversorgung	Mit Netzadapter
Eingangsspannung	100 - 240 AC
Eingangsstrom	1.5 A

Ausgangsspannung	12V DC
Ausgangsstrom	5 A
Polarität der Mittelspitze	Positiv
Steckertyp	M
Stromverbrauch	60

Umgebungsbedingungen

Betriebstemperatur	5°C to 35°C (41°F to 95°F)
Lagertemperatur	-20°C to 50°C (-4°F to 122°F)
Feuchtigkeit	20~80% RH

Physische Eigenschaften

Farbe	Schwarz
Gehäusotyp	Aluminium
Produktlänge	4.3 in [11.0 cm]
Produktbreite	1.8 in [4.5 cm]
Produkthöhe	0.9 in [2.4 cm]
Produktgewicht	4.4 oz [124.0 g]

Verpackungsinformationen

Paketmenge	1
Paketlänge	9.4 in [24.0 cm]
Paketbreite	4.1 in [10.5 cm]
Pakethöhe	3.8 in [9.6 cm]
Versandgewicht (Verpackung)	1.4 lb [0.6 kg]

Verpackungsinhalt

Im Paket enthalten	1 - USB Charging Station
	1 - Wallmount Bracket
	4 - Rubber Feet
	4 - Montageschrauben
	1 - Instruction Manual
	1 - Power Adapter

Garantieinformationen

Warranty	2 Jahre
----------	---------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.