

## 7-Port Charging Station for USB Devices

**Product ID:** ST7CU35122



This USB charging station lets you set up an external, multiport dedicated station for charging tablets, smartphones and other mobile devices.

This station is a standalone device that provides 5 x 1A and 2 x 2A USB charging ports, enabling you to charge multiple devices. The charging station can deliver the fastest possible power output required for each connected device. Note that some devices do not draw the full 1A or 2A of power, which enables more devices to be connected and charging at one time.

The charger also supports USB Battery Charging Specification 1.2, which ensures compatibility with a broad range of mobile devices, including the Apple iPhone and iPad, the Microsoft Surface tablet, the Samsung Galaxy Tab, Android devices and more.

The charge station is an ideal solution for charging your mobile devices during meetings in boardrooms, conference rooms, or lobbies. It gives you and your colleagues vital charging access when it's needed most. Plus, consolidating your USB devices onto a single multiport USB charger offers a more energy-efficient solution and avoids the need for multiple wall outlets or power bars, saving valuable space.

The compact, metal enclosure is extremely durable and offers simple operation using an integrated on/off power button that turns all ports on and off.

This hub is the perfect accessory for a laptop or desktop workstation, with a rugged metal housing that can withstand the wear and tear of daily use.

With the included wall-mount bracket, you can attach the hub to a surface such as a desktop or wall, to better suit your needs.

The StarTech.com ST7CU35122 is backed by a 2-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility

## Applications

- Use in IT helpdesk or tech bench environments to charge multiple tablets, smartphones or other USB devices
- Setup a USB charging station at home for the whole family
- Installation in locations where USB-A ports need to be securely mounted to a surface, such as a wall or on a desk

## Features

- No PC connection required
- Charge multiple devices with dedicated charging ports - 5 x 1A, 2 x 2A
- Integrated physical On/Off power button
- Supports USB Battery Charging Specification 1.2, including Apple and Samsung Galaxy devices
- Compact, metal enclosure
- Includes bracket for surface or wall-mount installation
- Save space and wall outlets using a consolidated charging station
- Includes universal power adapter

---

### Hardware

Warranty	2 Years
Ports	7
Industry Standards	USB Battery Charging Specification Rev. 1.2

---

### Connector(s)

Connector Type(s)	USB Type-A (4 pin) USB 2.0
-------------------	----------------------------

---

### Special Notes / Requirements

Note	The ST7CU35122 supports a maximum of 36 watts, which allows a maximum of up to four high-powered devices to be connected and charging at any one time (2x 1A and 2x 2A).
------	--


---

### Indicators

LED Indicators	Power
----------------	-------

---

### Power



Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	1.5 A
Output Voltage	12V DC
Output Current	3 A
Center Tip Polarity	Positive
Plug Type	M
Power Consumption (In Watts)	36

---

#### Environmental

Operating Temperature	5C to 35C (41F to 95F)
Storage Temperature	-20C to 50C (-4F to 122F)
Humidity	20~80% RH

---

#### Physical Characteristics

Color	Black
Material	Aluminum
Product Length	4.3 in [11.0 cm]
Product Width	1.8 in [45.0 mm]
Product Height	0.9 in [24.0 mm]
Weight of Product	4.4 oz [126.0 g]

---

#### Packaging Information

Package Quantity	1
Package Length	6.6 in [16.7 cm]
Package Width	4.1 in [10.5 cm]
Package Height	3.5 in [88.0 mm]
Shipping (Package) Weight	19.2 oz [545.0 g]



---

**What's in the  
Box**

Included in Package	
	USB Charging Station
	Instruction Manual
	Universal Power Adapter (NA/JP, EU, UK, ANZ)
	Wall-Mount Bracket (w/ Screws)
	Rubber Feet

---

***\*Product appearance and specifications are subject to change without notice.***

