

8-Port Charging Station for USB Devices - 96W/19.2A

Produkt-ID: ST8CU824



This USB charging station offers a high-powered solution for keeping your mobile devices powered and ready for use. It's compatible with a wide range of tablets and smartphones, and features built-in safety measures to help protect against damage to your mobile devices.

The charging station can deliver 96 watts of power in total, providing 2.4 amps of power per port. That means you can charge eight tablets at once, and every port can provide the power each device needs.

The charger supports USB Battery Charging Specification 1.2, which ensures compatibility with a broad range of mobile devices, including the Apple iPhone and iPad, the Microsoft® Surface™ tablet, the Samsung Galaxy Tab™, Android™ devices and more.

This all-in-one charger is perfect for charging multiple devices during meetings in a boardroom or conference room. It gives you and your co-workers access to charging when it's needed. Plus, consolidating your USB devices onto a single multi-port USB charger offers a more efficient solution and saves space because you don't need to use multiple wall outlets or power bars.

The compact, metal enclosure is extremely durable and offers simple operation using an integrated on/off power button that turns all ports on and off. For further flexibility, the charge station includes a bracket for wall-mounted installations.

The USB charging station features built-in safety measures to ensure that all of your devices are protected against damage from overheating, overvoltage, overcurrent or short circuiting. If the 96-watt limit is exceeded, the power being sent to the connected devices will turn off and the charger will reset itself until the load is reduced to safe levels. Plus, the charging station includes an internal fan which controls the temperature of the device in order to prevent overheating. The fan is automatically controlled to reduce noise levels.

The charger also includes an LED indicator beside each port to notify you of a short circuit, while the affected port will shut down until you power-cycle the charger.

The ST8CU824 is backed by StarTech.com's 2-year warranty and free lifetime technical support.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Charge up to eight mobile devices at once
- Use in IT helpdesk or tech-bench environments to charge multiple tablets, smartphones or other USB devices simultaneously
- Charge and deploy a fleet of tablets for mobile sales staff
- Set up a USB charging station at home for the whole family
- Install in locations where USB ports need to be securely mounted to a surface, such as a wall or on a desk

Merkmale

- Charge almost any mobile device with USB Battery Charging Specification 1.2 support
- Deliver the fastest possible power output required for each connected device, up to a total of 96 watts (19.2 amps) shared between all eight ports
- Save space and wall outlets, using a single, consolidated charging station

Hardware

Garantiebestimmungen 2 Years

Ports 8

Industrienormen USB Battery Charging Specification Rev. 1.2

Steckverbinder

Steckverbindertyp(en) 8 - USB 2.0 Typ-A (4 pin, 480Mbit/s)

Anzeiger

LED-Anzeiger 1 - Power

8 - Short circuit fault indicator beside each port

 Strom

Stromversorgung	Mit Netzadapter
Eingangsspannung	100 - 240 AC
Eingangsstrom	3A
Ausgangsspannung	12V DC
Ausgangsstrom	8A
Steckertyp	M
Stromverbrauch	96

Umgebungsbedingungen

Betriebstemperatur	5°C to 35°C (41°F to 95°F)
Lagertemperatur	-20°C to 50°C (-4°F to 122°F)
Feuchtigkeit	20~80% RH

Physische Eigenschaften

Farbe	Schwarz
Gehäusetyp	Aluminium
Produktlänge	8.3 in [21.2 cm]
Produktbreite	2.4 in [6.0 cm]
Produkthöhe	1.0 in [2.5 cm]
Produktgewicht	9.2 oz [262.0 g]

Verpackungsinformationen

Paketmenge	1
Paketlänge	9.4 in [23.9 cm]
Paketbreite	6.0 in [15.2 cm]

Pakethöhe 2.9 in [7.3 cm]

Versandgewicht 2.2 lb [1.0 kg]
(Verpackung)

Verpackungsinhalt

Im Paket enthalten

- 1 - USB Charging Station
- 2 - Wall-Mount Brackets
- 1 - Power Adapter
- 2 - Rubber Feet
- 4 - Mounting Screws

Garantieinformationen

Warranty 2 Jahre

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.