

2 Port Black PS/2 KVM Switch Kit with Cables

Product ID: SV211K



This 2 Port KVM Switch Kit lets you control two computers using a single keyboard, mouse and VGA monitor and offers both hotkey and top panel push-button operation for simple switching between connected computers.

Designed to integrate seamlessly into any environment, the KVM switch offers a small footprint design (roughly the size of a deck of playing cards) and draws power from the connected computers, so it doesn't require an external power supply.

A suitable solution for virtually any application, the KVM switch supports video resolutions of up to 2048 x 1536 and includes 3-in-1 (PS/2 and Video) cables to provide a complete, out-of-the-box KVM solution.

Delivering dependable and convenient control of multiple computers from a single peripheral station, this high quality KVM switch is backed by StarTech.com's 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Perfect for integrating two different enterprise computer systems.
- Useful for call centers, help desks, education environments, home gamers and PC enthusiasts.

Features

- All cables come out of the rear of the switch unlike competitor 3-sided "octopus" designs.
- Hot plug - computers can be added without resetting switches or other connected computers.

- Includes two (2) 6 ft. cables.

Hardware

Warranty	2 Years
Audio	No
KVM Ports	2
PC Interface	PS/2
PC Video Type	VGA
Number of Monitors Supported	1
Rack-Mountable	No
Cables Included	Yes
Daisy-Chain	No

Performance

DVI Support	No
IP Control	No
Hot-Key Selection	No
Maximum Cable Length	6.0 ft [1.8 m]
Maximum Analog Resolutions	1920 x 1440
Auto Scan	3, 8, 15 & 30 seconds
Maximum Number of Users	1

Connector(s)

Console Interface(s)	VGA (15 pin, High Density D-Sub) PS/2 (6 pin, Mini-DIN)
Host Connectors	VGA (15 pin, High Density D-Sub)

Software

OS Compatibility	OS independent; No software or drivers required
------------------	---

Special Notes / Requirements

Note	Optional Power Adapter requires 9V DC, 600 mA, center positive
------	--

Power

Power Source	Not Included (not required for standard applications)
--------------	---

Physical Characteristics

Color	Black
Material	Plastic
Product Length	6.3 in [16 cm]
Product Width	2.8 in [70 mm]
Product Height	0.8 in [21 mm]

Packaging Information

Package Length	8.6 in [21.8 cm]
Package Width	3.9 in [100 mm]
Package Height	3.8 in [96 mm]
Shipping (Package) Weight	25.8 oz [730 g]

What's in the Box

Included in Package	2 Port PS/2 KVM Switch Kit with Cables
	Cables
	Rubber Feet
	Instruction Manual

**Product appearance and specifications are subject to change without notice.*

