

## 4 Port Tower Style PS/2 KVM Switch Kit with Cables

**Product ID:** SV411KT




This 4-port tower style KVM Switch Kit lets you control multiple PS/2 computers from a single console (keyboard, mouse, monitor), saving equipment costs while providing a convenient operating platform.

A perfect console-sharing solution for SOHO, help desks and call centers, the KVM switch supports display resolutions of up to 1920x1440 as well as plug-and-play connectivity, which eliminates the hassle of having to power down computers to be connected to the switch. To ensure error-free bootups, the KVM switch supports PS/2 keyboard and mouse emulation.

The KVM switch offers both keyboard hotkey and front panel push-button control, and features a compact and lightweight mini-tower design with rear panel cable connections, saving valuable workspace.

Providing an out-of-the-box KVM solution, the tower style switch includes four 3-in-1 tangle-free cables and is backed by StarTech.com's 2-year warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Lets you instantly control four PS/2 computers from a single keyboard, mouse and monitor

- Compatible with desktops, workstations, servers, and laptops
- Useful for call centers, help desks, education environments, home gamers and PC enthusiasts

## Features

- Unique 3-in-1 cables prevent keyboard and mouse connectors from becoming loose
- Lightweight, compact mini tower
- Rear cable connections keep your desktop neat and tangle free
- Supports PS/2 keyboard and mouse emulation for error-free PC bootup
- Hot pluggable keyboard and mouse ports allow easy connections without having to reboot your systems
- Compatible with all operating systems
- Supports high VGA resolution of up to 1920x1440
- Power-free operation, draws power from attached computers and requires no external power adapters
- Port selection using push button or keyboard commands
- Supports Logitech Mouseman, and MS Intellimouse (Ver 2.0 and earlier).
- Supports PS/2 keyboard and mouse emulation for error-free PC bootup
- Draws power from computer, requiring no external power adapter

---

## Hardware

Warranty	2 Years
Audio	No
KVM Ports	4
PC Interface	PS/2
PC Video Type	VGA
Number of Monitors Supported	1
Rack-Mountable	No
Cables Included	Yes
Industry Standards	DDC2B

	Daisy-Chain	No
<b>Performance</b>		
	DVI Support	No
	IP Control	No
	Hot-Key Selection	Yes
	Maximum Analog Resolutions	1920x1440
	Auto Scan	3, 8, 15 & 30 seconds
	Maximum Number of Users	1
	Port Selection Support	Push Button and Hotkeys
<b>Connector(s)</b>		
	Console Interface(s)	2 - PS/2 (6 pin, Mini-DIN) 1 - VGA (15 pin, High Density D-Sub)
	Host Connectors	4 - VGA (15 pin, High Density D-Sub)
<b>Software</b>		
	OS Compatibility	OS independent; No software or drivers required
<b>Indicators</b>		
	LED Indicators	4 - Port Status
<b>Physical Characteristics</b>		
	Color	Black
	Material	Plastic
	Product Length	3.9 in [10 cm]
	Product Width	2.0 in [5 cm]
	Product Height	5.0 in [12.6 cm]
	Product Depth	3.9 in [100 mm]
	Weight of Product	7.2 oz [204 g]

---

**Packaging Information**

Package Length	9.9 in [25.2 cm]
Package Width	3.8 in [96 mm]
Package Height	7.3 in [18.6 cm]
Shipping (Package) Weight	2.7 lb [1.2 kg]

---

**What's in the Box**

Included in Package	1 - 4 Port KVM
	4 - 6ft(1.83m) KVM Cables
	1 - User Manual

---

***\*Product appearance and specifications are subject to change without notice.***