

## USB VGA KVM Console Extender w/ Serial & Audio Over Cat5 UTP - 1000 ft

**Product ID:** SV565UTPUSA



The SV565UTPUSA USB VGA KVM Console Extender w/ Serial & Audio Over Cat5 UTP (1000 ft) lets you control a server, computer or multiple computers (connected through KVM Switch) over standard Cat5 or Cat6 UTP network cable, at distances of up to 1000ft (333m) over a secure remote connection to a locked (secure) server.


Attached mounting brackets on the remote unit allow the console extender to be mounted in a convenient location, and features support for resolutions up to 1920x1080, with automatic image calibrations for out-of-the-box performance and manual controls accessible via the serial interface.

For added convenience, the Console/KVM extender supports USB computer connections, and is compatible with any brand of USB KVM Switch.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Connectivity Model

### Certifications, Reports and Compatibility



### Applications

- Ideal for high security environments where the server and data contained within a server room, while the user has no direct access to the hardware
- Extend USB keyboard and mouse, RS232 serial, VGA, and audio up to 1000ft away
- Monitor computer-controlled equipment in a factory or warehouse
- Use one or more servers in a server room from a remote location<br>
- Perfect for adding console controls for areas not environmentally suitable for a full PC or server
- Can act as a thin client for power users controlling powerful rack mounted servers as their desktop machines
- Full serial support for remote applications such as touchscreens, barcode scanners, etc.

## Features

- Maximum supported distance of 1000ft (300m)
- Automatic image calibration and adjustment
- Upgradable Firmware
- Manual configuration via serial interface
- VGA and Audio pass through on remote unit
- Serial devices can be connected at the local station or the remote console
- Supports cascading for multiple remote stations
- Supports most combo keyboard and mouse sets (including Wireless)
- High resolution support up to 1920 x 1080 @60Hz
- Wall Mounting brackets on remote unit
- Transmitter unit is powered by the USB port of the host PC; the remote unit is powered by it's own adapter.

---

## Hardware

Warranty	2 Years
Audio	Yes
KVM Ports	1
PC Interface	USB
PC Video Type	VGA

	Number of Monitors Supported	1
	Rack-Mountable	No
	Daisy-Chain	Yes
<b>Performance</b>		
	IP Control	No
	Max Transfer Distance	300m [984ft]
	Maximum Analog Resolutions	1920 x 1080 @60Hz
<b>Connector(s)</b>		
	Console Interface(s)	2 - 3.5 mm Mini-Jack (3 Position) 1 - DB-9 (9 pin, D-Sub) 2 - RJ-45 2 - USB 2.0 Type-A (4 pin, 480Mbps) 1 - VGA (15 pin, High Density D-Sub)
	Host Connectors	2 - 3.5 mm Mini-Jack (3 Position) 1 - DB-9 (9 pin, D-Sub) 1 - RJ-45 1 - USB B (4 pin) 1 - VGA (15 pin, High Density D-Sub)
	Other Interface(s)	1 - 3.5 mm Mini-Jack (3 Position) 1 - VGA (15 pin, High Density D-Sub)
<b>Software</b>		
	OS Compatibility	OS independent; No software or drivers required
<b>Special Notes / Requirements</b>		
	Note	Supports most combo keyboard and mouse sets (including Wireless)
<b>Indicators</b>		

LED Indicators	RJ45 Link LED (Local and Remote)
	USB Link (Keyboard and Mouse on Local, Single USB on Remote)
	Power LED Link (Receiver and Transmitter)
	Setup LED (Local)

---

## Power

Power Source	AC Adapter Included
Input Voltage	110V-240V AC
Input Current	0.8A
Output Voltage	5 DC
Output Current	4A
Center Tip Polarity	Positive
Plug Type	N
Power Consumption (In Watts)	20

---

## Environmental

Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-40C to 70C (-40F to 158F)
Humidity	80% RH

---

## Physical Characteristics

Color	Black
Material	Aluminum
Product Width	6.1 in [15.6 cm]
Product Height	1.0 in [2.6 cm]
Product Depth	4.4 in [112 mm]
Weight of Product	10.4 oz [296 g]

---

## Packaging

## Information

Package Quantity	1
Package Length	8.7 in [22 cm]
Package Width	7.9 in [20 cm]
Package Height	1.5 in [37 mm]
Shipping (Package) Weight	10.8 oz [305 g]

## What's in the Box

Included in Package	1 - Local Receiver
	1 - Remote Transmitter
	1 - USB Cable
	1 - VGA cable
	1 - Power Adapter
	1 - Instruction Manual

## Warranty Information

Warranty	2 Years
----------	---------

***\*Product appearance and specifications are subject to change without notice.***