

DC Power Adapter - 12V, 5A

Product ID: SVA12M5NA



This replacement power adapter can provide a power source for any electronic device that has an M type barrel jack and requires 12 volts and up to 5 amps of power.

The adapter is a perfect replacement for the lost or damaged power adapter you've used to power your existing electronics.

When downtime isn't an option, keeping spare power adapters on hand ensures that you won't be left waiting for a replacement to arrive or have to replace your devices just for the sake of a compatible power source.

This power adapter is a direct replacement for the power adapters included with the following StarTech.com products:

Conference Table Box for AV Connectivity
10 Gigabit Ethernet Copper-to-Fiber Media Converter
Fiber Media Converter Gigabit 1000Mbps MM Fibre LC 550m
Gigabit Ethernet Copper-to-Fiber Media Converter SM LC 10 km
Gigabit Ethernet Copper-to-Fiber Media Converter - SM LC 20 km
Multi-Input to HDMI Automatic Switch and Converter 4K
1U 17 in. HD 1080p Rackmount LCD Console with Front USB Hub
1U 19in Rackmount LCD Console with Integrated 8 Port KVM Switch
USB 3.0 SATA Hard Drive Duplicator & Eraser Dock
HDMI over CAT5 HDBaseT Extender
4K HDMI over CAT5 HDBaseT Extender
HDMI Over CAT5/CAT6 Extender with Power Over Cable
HDMI over CAT5 HDBaseT Extender RS232 IR Ultra HD 4K 330 ft
4-Port Industrial USB 3.0 Hub
4-Port Charging Station for USB Devices
7-Port USB 3.0 Hub - Desktop or Wall-Mountable Metal Enclosure
7-Port USB 3.0 Hub - Desktop
2 Port Dual DVI USB KVM Switch with Audio & USB 2.0 Hub
2 Port DVI VGA Dual Monitor KVM Switch USB with Audio & USB 2.0 Hub
2 Port Dual DisplayPort USB KVM Switch with Audio & USB 2.0 Hub
4 Port Dual DVI USB KVM Switch with Audio & USB 2.0 Hub

The SVA12M5NA is backed by a 2-year StarTech.com warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Replace a lost or broken power adapter
- Keep an extra power adapter on hand for your mission-critical devices
- Use a single power adapter as you travel between multiple regions

Features

- Supports a range of devices that require 12 volts and 5 amps (or less) of power and an M-type barrel connector
- Reduces downtime in the event of a failure, by keeping a spare power adapter on-hand

Power


Warranty	2 Years
Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	2 A
Output Voltage	12V DC
Output Current	5 A
Center Tip Polarity	Positive
Plug Type	M

Physical Characteristics

Cable Length	3.3 ft [1.0 m]
Product Length	4.3 in [11.0 cm]
Product Width	1.8 in [46.0 mm]
Product Height	1.4 in [35.0 mm]
Weight of Product	32.0 oz [905.8 g]

Packaging Information

Package Length	12.6 in [32.0 cm]
Package Width	8.7 in [22.0 cm]



Package Height 2.0 in [51.0 mm]

Shipping (Package) Weight 32.6 oz [924.2 g]

What's in the Box

Included in Package universal power adapter (NA/JP, EU, UK, AU)

****Product appearance and specifications are subject to change without notice.***

