

2 Port USB KM Switch - USB Keyboard and Mouse Switch with File Transfer

Product ID: SVKMS



The SVKMS 2-Port USB KM Switch (Keyboard/Mouse) Sharing Cable with File Transfer enables you to control two computer systems using a single keyboard and mouse set, and offers the ability to transfer files between the connected systems.

Offering automated installation (no additional software or drivers required), this compact keyboard/mouse switch connects your systems using a standard USB 2.0 port to make switching between systems as simple as moving the mouse over to your second display, or using hot-keys.

This simple KM link cable also provides the added benefits of clipboard sharing so you can copy and paste text from one system to another, and drag and drop files for effortless transfers and data management.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Perfect for office applications where multiple computers need to be controlled by a single user and desk space is limited
- Great for PC repair or tech bench environments, allowing you to control and monitor two systems simultaneously
- A convenient solution for the business user needing to transfer files between their desktop and laptop systems

Features

- Keyboard and mouse sharing between 2 computers

- Simple switching between systems via mouse movement, hot-keys or hot-click area
- Drag and drop file transfer
- Copy and paste text between systems
- Plug-and-Play, no software/driver CD required

Hardware

Warranty	2 Years
KVM Ports	2
PC Interface	USB
Rack-Mountable	No
Cables Included	Yes
Chipset ID	OTi - 2211
Daisy-Chain	No

Performance

On-Screen Display	No
IP Control	No
Hot-Key Selection	Yes
Maximum Number of Users	1

Connector(s)

Host Connectors	USB Type-A (4 pin) USB 2.0
-----------------	----------------------------

Software

OS Compatibility	Windows 8 (32/64bit), 7 (32/64)/ Vista(32/64)/ XP(32/64)
Microsoft WHQL Certified	Yes

Special Notes / Requirements

Note	Mac OSX support is limited. Only Windows to Mac KM sharing is supported. Mac to Mac is not supported. OSX does not support file transfers or clipboard sharing.
------	---



Indicators

LED Indicators	Connection/activity indicators
----------------	--------------------------------

Environmental

Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-10C to 60C (14F to 140F)
Humidity	80% RH

Physical Characteristics

Color	Black
Material	Plastic
Product Length	4.0 ft [1.2 m]
Product Width	0.8 in [20.5 mm]
Product Height	0.4 in [10.5 mm]
Weight of Product	1.1 oz [32 g]

Packaging Information

Package Length	5.6 in [14.2 cm]
Package Width	6.7 in [17 cm]
Package Height	1.3 in [33 mm]
Shipping (Package) Weight	3.8 oz [108 g]

What's in the Box

Included in Package	Keyboard Mouse Sharing Cable
	Instruction Manual

****Product appearance and specifications are subject to change without notice.***

