

25 ft 3-in-1 Universal PS/2 KVM Cable

Productcode: SVPS23N1_25



StarTech.com's universal series PS/2 KVM switch cables prevent tangles and keep your workspace neat while delivering excellent performance with your StarTech.com StarView or other KVM switch.

This 25ft 3-in-1 PS/2 KVM switch Cable is constructed of high quality materials and is expertly designed to ensure crystal clear display quality, and durable performance. Like all StarTech.com cables, this product comes with a Lifetime warranty.

Works with:

Compatible StarTech.com KVMs can be found under the Accessories section.

Aten models (CS78, CS9134, CS9138, CS138A, CS88A, CS82A, CS84A, CS12, CS14, CS124A, CS114A)

Tripplite models (B007-008)

Cables to go models (32569, 22391)

IOGear models (GCS82B, GCS138, GCS78KIT, GCS78, GCS138KITUP, GCS138KIT)

Certificaties, rapporten en compatibiliteit



Toepassingen

- KVM switch cable to be used with OmniView, StarView, SwitchView and Apex KVM switches. (Note: Some non-StarView models may require gender changing cable adapters.)

Eigenschappen

- KVM (Keyboard-Video-Mouse) switch cables allows you to connect your computers to a KVM switch
- High quality video cable uses coaxial and twisted pair wiring to maintain optimal video signals
- Ferrite cores at both ends of video cable minimizes electromagnetic interference and provides crystal clear video
- Available in AT- and PS/2-styles in various cable lengths

Connector(en)

Garantiebeleid	Lifetime
Connector A	2 - PS/2 (6-polig, Mini-DIN) 1 - VGA (15-polig, D-Sub met hoge dichtheid)
Connector B	2 - PS/2 (6-polig, Mini-DIN) 1 - VGA (15-polig, D-Sub met hoge dichtheid)

Fysieke eigenschappen

Kabellengte	25.0 ft [7.6 m]
Gewicht product	3.0 lb [1.4 kg]

Verpakkingsinformatie

Lengte Verpakking	13.7 in [34.7 cm]
Package Width	0.9 in [23.6 mm]
Package Height	18.1 in [46 cm]
Verzendgewicht (verpakt)	3.2 lb [1.4 kg]

Wat wordt er

meegeleverd

Meegeleverd

1 - 25 FT PS/2 STYLE 3-IN-1 KVM SWITCH CABLE

1 - DB15 male/male gender changer (GC15HSM)

1 - metal part of thumbscrew must be 1.17in(3cm)

1 - THUMBSCREWS MUST BE 1.93 inches long (4.9cm)
THUMBSCREWS MUST BE 1.93in(4.9cm)

Garantiebepalinge
n

Warranty

Levenslang

* Uitvoering en specificaties van het product zijn zonder aankondiging vatbaar voor wijzigingen.