

Thunderbolt to eSATA plus USB 3.0 Adapter - Thunderbolt Adapter

Product ID: TB2USB3ES



The TB2USB3ES Thunderbolt to eSATA + USB 3.0 Adapter lets you expand your MacBook or laptop connectivity by combining Thunderbolt to eSATA and Thunderbolt to USB 3.0 functionality into a single, compact adapter. You gain two vital interfaces that are unavailable or limited on most Thunderbolt-equipped systems, delivering fast, reliable performance, more connection possibilities, and rugged portability.

Experience fast, effective and reliable performance from your essential peripherals! Now, you can leverage the 10 Gbps bandwidth of your Thunderbolt port to create a scalable, high-speed solution that offers eSATA and USB 3.0 connectivity.

To maximize efficiency, two dedicated lanes connect the Thunderbolt adapter directly to your system PCIe bus. Each lane delivers 5 Gbps bandwidth so you effectively avoid performance bottlenecks when both ports are in use. This versatile adapter gives you fast, simple and reliable external connectivity, offered by revolutionary Thunderbolt technology.

Take full advantage of your current peripherals! Saving you the added expense of purchasing new devices, this single adapter lets you simultaneously connect your existing peripherals through your Thunderbolt port - perfect for eSATA external hard drives (with SATA III support), as well as USB 3.0 hubs (with UASP support), or for syncing with your tablet or smartphone.

You can even integrate the adapter into the end of a Thunderbolt daisy-chain configuration! Connect the adapter to your Thunderbolt Docking Station (SKU: TBDOCKHDPBC - sold separately), for further MacBook expandability!

Get work done on the go, and look great doing it! A rugged and travel-friendly design lets you tuck the adapter neatly into your laptop bag, plus the casing combines portability with durability to offer quality protection that lets you take the adapter anywhere.

This sleek and stylish Thunderbolt adapter aesthetically matches your MacBook Pro or MacBook Air, with a silver sandblast finish and black rubberized grips. Plus, the compact adapter requires no external power, and integrates a built-in Thunderbolt cable as well as hassle-free plug-and-play installation.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

[View more](#)

Certifications, Reports and Compatibility

Applications

- Add 2 essential connectivity ports to your Thunderbolt-equipped MacBook Pro, MacBook Air, laptop or Ultrabook
- Connect an eSATA-equipped external hard drive, or external enclosure to your laptop via a Thunderbolt port
- Add an extra USB 3.0 port to connect your peripherals at home, in the office or while traveling
- Perfect for use with your MacBook or laptop in a shared workspace or hot desk environment

Features

- 1 x eSATA (5Gbps) and 1 x USB 3.0 port (5Gbps), through a Thunderbolt connection
- Compact and durable case design with an integrated Thunderbolt cable, for maximum portability
- Supports Thunderbolt data rates of up to 10Gbps, with 2 dedicated PCI Express lanes (one per port)
- Hassle-free setup - Plug-and-play installation on supported operating systems using native drivers
- eSATA port supports SATA III / II / I connections
- USB 3.0 port supports UASP and is backward compatible with USB 2.0
- Silver sandblast finish with rubberized grips, matching Apple MacBooks
- Bus-powered - No external power required

Hardware

Warranty	2 Years
Ports	2
Interface	eSATA USB 3.0
Bus Type	Thunderbolt
Chipset ID	Intel - DSL2210 ASMedia - ASM1061

ASMedia - ASM1042A

Performance

Maximum Data Transfer Rate	10 Gbps (Thunderbolt)
	5 Gbps (eSATA)
	5 Gbps (USB 3.0)
Type and Rate	Thunderbolt - 10 Gbit/s
UASP Support	Yes
Type and Rate	SATA III (6 Gbps)
Port Multiplier	Yes
LBA support	48-bit
Hardware Raid Supported	No

Connector(s)

Connector Type(s)	eSATA (7 pin, Data)
	Thunderbolt (20-pin)
	USB Type-A (9 pin) USB 3.0 (5 Gbps)

Software

OS Compatibility	Windows 8, 8.1, 10
	Mac OS 10.8.4 to 10.13

Environmental

Operating Temperature	-10C to 55C (14F to 131F)
Storage Temperature	-20C to 85C (-4F to 185F)

Physical Characteristics

Color	Silver
Material	Plastic
Cable Length	5.1 in [13 cm]
Product Length	3.1 in [78 mm]



Product Width	1.9 in [48.5 mm]
Product Height	0.8 in [20.5 mm]
Weight of Product	2.6 oz [73 g]

Packaging Information

Package Length	6.9 in [17.5 cm]
Package Width	5.5 in [14 cm]
Package Height	1.3 in [32 mm]
Shipping (Package) Weight	5.7 oz [161 g]

What's in the Box

Included in Package	Thunderbolt Adapter
	Instruction Manual

****Product appearance and specifications are subject to change without notice.***

