

Dual 4K Monitor Mini Thunderbolt 3 Dock with HDMI - Mac & Windows Docking Station - Discontinued, Limited Stock, & Replaced by TB3DKM2HDL (TB3DKM2HD)

Product ID: TB3DKM2HD



This Thunderbolt 3 docking station packs big performance into a cost-effective, compact mini dock, delivering essential connections for productivity. The bus-powered Thunderbolt 3 dock lets you connect to dual 4K HDMI displays, Gigabit Ethernet and two USB (Type-A) ports and for a flexible setup, the attached USB-C cable has an extended length of (7.9 in./ 20 cm).

Great for editing 4K video or other Ultra HD tasks, this portable Thunderbolt 3 to HDMI dock supports 40Gbps of throughput and 4K resolution at 60Hz on dual HDMI monitors, through a single Thunderbolt 3 port. Run resource-demanding applications on two independent displays without draining system resources.

Connect your laptop to:

- 2x 4K HDMI displays (up to 4096 x 2160p @ 60Hz)

Simply connect the TB3 dock to your laptop with included TB3 cable and start working immediately. No time-consuming driver installations are required.

To enhance your productivity, the Gigabit Ethernet port (with PXE Boot and Wake-on-LAN support) ensures reliable wired network access. A USB 3.0 Type-A port, with ample space around it, lets you connect a USB device, such as a flash drive, for easy file access. Connect another USB device using the USB 2.0 Type-A port.

The TB3DKM2HD is Thunderbolt Certified, and backed by a StarTech.com 3-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility





Applications

- Review/edit images or media files on two 4K HDMI displays
- Transfer a 4K movie in under 30 seconds
- Ideal for shared or temporary work stations, such as hot desks (hoteling)

Features

- Add dual UHD 4K HDMI monitors at 60Hz to your laptop with this portable Thunderbolt 3 docking station
- Connect your devices with 2x USB-A ports - 1x USB 3.0 and 1x USB 2.0
- Add wired network connectivity with the Gigabit Ethernet RJ45 port
- Bus-powered (no external power required) via extended length 7.8 in. (20 cm) cable
- Compact design in durable aluminum
- Easy to set up and ready to go with no driver installation required

Hardware	Warranty	3 Years
	4K Support	Yes
	Fast-Charge Port(s)	No
	Displays Supported	2
	Bus Type	Thunderbolt 3
	Industry Standards	Thunderbolt 3
	Chipset ID	IEEE 802.3, IEEE 802.3u, IEEE 802.3ab
		USB 3.0 - Backward compatible with USB 2.0 and 1.1
		USB 2.0 - Backward compatible with 1.1
		Intel - Alpine Ridge JHL6540
		Intel - WGI210AT
		Texas Instruments - TPS65983
		ASMedia - ASM1042A
	Parade - PS176	
Performance	Maximum Data Transfer Rate	40 Gbps (Thunderbolt 3) 5 Gbps (USB 3.0)
	Maximum Digital Resolutions	2 Gbps (Ethernet; Full-Duplex)
	Type and Rate	Dual 4K displays - HDMI 4096 x 2160p @ 60Hz / 3840 x 2160p @ 60Hz

UASP Support	Thunderbolt 3 - 40 Gbit/s
Compatible Networks	Yes
Auto MDIX	10/100/1000 Mbps
PXE	Yes
Full Duplex Support	Yes
	Yes

Connector(s)	Connector Type(s)	Thunderbolt 3 USB-C (24-pin) (40Gbps)
	Connector Type(s)	HDMI (19 pin)
	Connector Type(s)	USB Type-A (9 pin) USB 3.0 (5 Gbps)
	Connector Type(s)	RJ-45
	Connector Type(s)	USB Type-A (4 pin) USB 2.0

Software	OS Compatibility	Windows 7, 8, 8.1, 10 >macOS 10.12 - 10.15
-----------------	------------------	---

Special Notes / Requirements	System and Cable Requirements	Thunderbolt 3 equipped computer with a Thunderbolt 3 port.
	Note	A 4K-capable display is required to achieve 4K x 2K resolution (4K is also known as 4K x 2K).

Power	Power Source	USB-Powered
--------------	--------------	-------------

Environmental	Operating Temperature	5C to 35C (41F to 95F)
	Storage Temperature	-40C to 70C (-40F to 158F)
	Humidity	5~95% RH (Non-condensing)

Physical Characteristics	Color	Black & Gray
	Material	Aluminum
	Cable Length	7.9 in [2 cm]
	Product Length	4.9 in [1.2 cm]
	Product Width	2.4 in [61.000 mm]
	Product Height	0.7 in [18.800 mm]
	Weight of Product	5.1 oz [145.800 g]

Packaging Information	Package Length	8.2 in [2.1 cm]
	Package Width	5.7 in [1.4 cm]

Package Height 1.4 in [36.000 mm]

Shipping (Package) Weight 9.2 oz [260.000 g]

What's in the Box	Included in Package	Docking Station
	Included in Package	User Manual

****Product appearance and specifications are subject to change without notice.***

