

USB S-Video and Composite Video Capture Device Cable with Audio

Product ID: SVID2USB2



The SVID2USB2 USB 2.0 S-Video/Composite video Capture Cable lets you connect devices that output S-Video or Composite video to a computer through an available USB 2.0 port. The cable also features two channel RCA stereo audio inputs that let you capture the audio accompanying the S-Video or Composite video signal.

The perfect solution for bridging a computer and an S-Video or Composite video source, the capture cable offers real time MPEG 1, MPEG 2 and MPEG 4 recording. Small enough to fit in the palm of your hand, the Capture Cable is a great solution for mobile applications that integrates seamlessly with laptop and desktop computers.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Convert VHS home movies to digital format
- Import recorded videos into your computer system for editing and make your own compilation
- Connect your VCR, camcorder, or any other analog video source to your desktop or notebook PC and capture your audio/video in MPEG 1/2/4 format

Features

- Small and lightweight for portability or on the go applications
- USB 2.0 transfer rates for high quality video capturing

- Choose from MPEG 1 / MPEG 2 / MPEG 4 video encoding
- Up to 30 fps motion capture capability at maximum resolution of 720x480(NTSC) / 720x576(PAL)
- Snapshot function allows you to capture still images
- Control brightness, contrast, and sharpness
- USB powered device - requires no external power adapter
- Supports NTSC, PAL, and SECAM

Hardware

Warranty	2 Years
AV Input	Composite S-Video Audio RCA
AV Output	USB
Audio	Yes
Industry Standards	Video Input: NTSC, PAL, SECAM Video Encoding: MPEG 1, MPEG 2, MPEG 4 DirectShow Compatible

Performance

Maximum Data Transfer Rate	480Mbps
Maximum Analog Resolutions	720x480(NTSC) / 720x576(PAL)

Connector(s)

Connector A	USB Type-A (4 pin) USB 2.0
Connector B	S-Video (4 pin, Mini-DIN) Composite Video (1 x RCA) Stereo Audio (2 x RCA)

Software

OS Compatibility	Windows 8/8.1 (32/64bit), 7 (32/64bit), Vista(32/64), XP(32/64),
------------------	--



2000

Special Notes / Requirements

Note	USB audio input is only supported with Windows XP and later. Previous operating systems will require audio input through a line in jack built-in to your sound card
	The SVID2USB2 can record up to a maximum 120min of video at a time

Physical Characteristics

Color	Black
Cable Length	34.0 in [86.4 cm]
Product Length	3.5 ft [1.1 m]
Product Width	1.2 in [30 mm]
Product Height	0.5 in [12 mm]
Weight of Product	2.7 oz [76 g]

Packaging Information

Package Length	11.7 in [29.8 cm]
Package Width	2.4 in [62 mm]
Package Height	7.8 in [19.8 cm]
Shipping (Package) Weight	15.9 oz [450 g]

What's in the Box

Included in Package	USB Video Capture Cable
	Software CD
	Driver CD
	Instruction Manual

****Product appearance and specifications are subject to change without notice.***

