

50 ft 3-in-1 Universal PS/2 KVM Cable

Product ID: SVPS23N1_50



StarTech.com's universal series PS/2 KVM switch cables prevent tangles and keep your workspace neat while delivering excellent performance with your StarTech.com StarView or other KVM switch.

This 50ft 3-in-1 PS/2 KVM switch Cable is constructed of high quality materials and is expertly designed to ensure crystal clear display quality, and durable performance. Like all StarTech.com cables, this product comes with a Lifetime warranty.

Works with:

Compatible StarTech.com KVMs can be found under the Accessories section.

Aten models (CS78, CS9134, CS9138, CS138A, CS88A, CS82A, CS84A, CS12, CS14, CS124A, CS114A)

Tripplite models (B007-008)

Cables to go models (32569, 22391)

IOGear models (GCS82B, GCS138, GCS78KIT, GCS78, GCS138KITUP, GCS138KIT)

Certifications, Reports and Compatibility



Applications

- KVM switch cable to be used with OmniView, StarView, SwitchView and Apex KVM switches. (Note: Some

non-StarView models may require gender changing cable adapters.)

Features

- KVM (Keyboard-Video-Mouse) switch cables allows you to connect your computers to a KVM switch
- High quality video cable uses coaxial and twisted pair wiring to maintain optimal video signals
- Ferrite cores at both ends of video cable minimizes electromagnetic interference and provides crystal clear video
- Available in AT- and PS/2-styles in various cable lengths

Connector(s)

Warranty	Lifetime
Connector A	2 - PS/2 (6 pin, Mini-DIN) 1 - VGA (15 pin, High Density D-Sub)
Connector B	2 - PS/2 (6 pin, Mini-DIN) 1 - VGA (15 pin, High Density D-Sub)

Physical Characteristics

Cable Length	50.0 ft [15.2 m]
--------------	------------------

Packaging Information

Package Length	13.7 in [34.8 cm]
Package Width	1.6 in [40 mm]
Package Height	18.1 in [46 cm]
Shipping (Package) Weight	4.8 lb [2.2 kg]

What's in the Box

Included in Package	1 - 50 FOOT PS/2 STYLE 3-in-1 KVM SWITCH CABLE 1 - DB15 male/male gender changer (GC15HSM) 1 - THUMBSCREWS MUST BE 1.93 inches long (4.9cm) THUMBSCREWS MUST BE 1.93in(4.9cm) 1 - metal part of thumbscrew must be 1.17in(3cm)
---------------------	--

****Product appearance and specifications are subject to change without notice.***