

0.8 m (2.7 ft.) Thunderbolt 3 to Thunderbolt 3 Cable - 40Gbps

Product ID: TBLT34MM80CM



This Thunderbolt 3 to Thunderbolt 3 cable lets you deliver video, data and power to your Thunderbolt 3, USB 3.2 and DisplayPort devices. At 0.8 meters in length, the Thunderbolt cable provides added flexibility and distance when connected to your devices.

Fully compatible with your USB 3.2 Gen 2 devices, this cable can be used for charging and syncing your mobile devices. Also, connect and power USB-C laptops, such as your MacBook or Chromebook, and USB-C peripherals, such as your docking station.

This Thunderbolt 3 USB-C cable supports data transfer rates up to 40Gbps when connected to a Thunderbolt 3 device, enabling lightning fast performance. When connected to a USB 3.2 device, this cable supports rates of 20Gbps.

This cable supports dual 4K 60Hz or full 5K 60Hz video for an astonishing resolution, contrast, and color depth.

The Thunderbolt 3 Type-C cable delivers up to 100W of power for charging a Thunderbolt 3 laptop, which means you can keep your devices powered without using an additional power supply.

Bridge multiple Thunderbolt 3 USB-C enabled laptops for peer-to-peer 10GbE networking with this cable. It's also perfect for sharing peripherals such as printers and storage.

TBLT34MM80CM is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Connect your Thunderbolt 3 devices

- Power and charge Thunderbolt 3 devices
- Charge USB 3.2 mobile devices
- Peer-to-peer networking for various Thunderbolt 3 laptops

Features

- Thunderbolt certified cable delivers full Thunderbolt 3 performance and compatibility
- Experience unbelievable data transfer rates of up to 40Gbps when connected to Thunderbolt 3 devices
- Enjoy astonishing resolution by connecting to either a 5K display or two 4K UHD monitors
- Supports single-cable docking while powering and charging your laptop at the same time
- Easily set up peer-to-peer networking with multiple Thunderbolt 3 laptops

Hardware

Warranty	2 Years
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

Performance

Type and Rate	Thunderbolt 3 - 40 Gbit/s
---------------	---------------------------

Connector(s)

Connector A	Thunderbolt 3 USB-C (24-pin) (40Gbps)
Connector B	Thunderbolt 3 USB-C (24-pin) (40Gbps)

Physical Characteristics

Color	Black
Cable Length	31.5 in [80 cm]
Product Length	31.5 in [80.1 cm]
Product Width	0.5 in [12.3 mm]
Product Height	0.3 in [6.4 mm]



Weight of Product	1.2 oz [35.0 g]
-------------------	-----------------

Packaging Information

Package Length	5.0 in [12.7 cm]
----------------	------------------

Package Width	8.6 in [21.9 cm]
---------------	------------------

Package Height	0.4 in [10.0 mm]
----------------	------------------

Shipping (Package) Weight	1.6 oz [44.0 g]
---------------------------	-----------------

What's in the Box

Included in Package	0.8 m Thunderbolt 3 Cable
---------------------	---------------------------

****Product appearance and specifications are subject to change without notice.***

