

USB-C to Gigabit Ethernet Adapter, Black, Thunderbolt 3 / 4 Compatible, Windows & Mac, RJ45 LAN Network Converter

Product ID: US1GC30B



Instantly add a Gigabit Ethernet network connection to your computer with a USB-C to Gigabit Ethernet adapter, using either the USB Type-C or Thunderbolt 3 port on your computer.

The USB-C to LAN adapter supports full Gigabit bandwidth by harnessing the performance of USB 3.2 Gen 1 (5Gbps). You can access very large files over the network at 10/100/1000Mbps network speeds with checksum offload (IPv4, IPv6, TCP, UDP) and large-send offload support.

Instantly delivers Gigabit speeds using the USB-C or Thunderbolt 3 port on your device without requiring an internal Ethernet card in your device.


Simply plug the network adapter into the USB-C port on your laptop and connect to your network. The adapter's Realtek RTL8153 chipset provides native driver support in Chrome OS, macOS and Windows.

This portable USB Gigabit network adapter is the ideal desktop network adapter or laptop accessory for those who require more portability. It's powered directly from the USB port making it easy to connect when you're on the go.

Our USB network adapters make it easy to add a wired network connection to your laptop, desktop or tablet. If your device has a USB port available, then our compact USB network adapters can help you connect. This USB Type-C to Ethernet adapter is backed by a 2-year warranty and free lifetime North American based Technical Support.

Certifications, Reports and Compatibility





Applications

- Small businesses
- Home offices
- Departmental networks
- Network gaming

Features

- **USB-C NETWORK ADAPTER:** USB-C to RJ45 adapter adds an Ethernet port to your computer supporting up to Gigabit speeds on 10/100/1000 Mbps Networks; Ideal for reliable wired gigabit network connections, or as an alternative to WiFi
- **FULL FEATURED:** USB-C to Ethernet dongle; Uses Realtek RTL8153 Chipset for native compatibility with laptops, desktops, and 2-in-1 computers; Compatible with USB C, Thunderbolt 3 and Thunderbolt 4
- **VERSATILE DESIGN:** With its compact and lightweight design for maximum portability, this USB Type-C NIC/Gigabit network adapter enables you to securely connect your laptop to a Gigabit Ethernet network wherever you go; USB bus-powered
- **TECHNICAL SPECS:** USB 3.2 Gen 1 Type-C (5 Gbps); Compatible with USB 3.0/2.0; 1x RJ45 Port; Attached Cable; 10/100/1000 Mbps; Realtek RTL8153 Chipset ; 9K Jumbo Frames; VLAN Tagging; Wake-on-LAN; Color: Black; No driver install required
- **OS COMPATIBILITY:** USB NIC adapter for laptop offers plug and play connectivity; Works with Windows versions 7 and up, Windows Server, macOS 10.14 and up, Linux with kernel 4.11 and up (LTS only), ChromeOS, Android and iOS (iPhone 15 [Plus/Pro/Max] and up)

Hardware

Warranty	2 Years
Ports	1

Interface	RJ45 (Gigabit Ethernet)
Bus Type	USB 3.2 Gen 1 (5 Gbps)
Industry Standards	IEEE 802.3, 802.3u and 802.3ab
Chipset ID	Realtek - RTL8153

Performance

Wake On Lan	Yes
Maximum Data Transfer Rate	5 Gbps (USB 3.0) 2 Gbps (Ethernet - Full-Duplex)
Type and Rate	USB 3.2 Gen 1 - 5 Gbit/s
Compatible Networks	10/100/1000 Mbps
Auto MDIX	Yes
Full Duplex Support	Yes

Connector(s)

Connector Type(s)	1 - USB 3.2 Type-C (24 pin, Gen 1, 5Gbps)
External Ports	1 - RJ-45

Software

OS Compatibility	Windows XP, Vista, 7, 8, 8.1, 10, 10 ARM, 11, 11 ARM Windows Server 2003, 2008 R2, 2012, 2016, 2019, 2022 macOS 10.7 to 10.15, 11.0, 12.0, 13.0, 14.0 <i>VLAN tagging is currently not supported in macOS</i> Linux Kernel 2.6.25 to 4.11.x <i>LTS Versions only</i> ChromeOS
------------------	-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

Special Notes / Requirements

System and Cable Requirements	Available USB Type-C port
Note	Jumbo Frames are no longer supported in macOS

Power

Power Source	USB-Powered
--------------	-------------

Input Voltage	5V DC
Output Voltage	5 DC

Environmental

Operating Temperature	0C to 45C (32F to 113F)
Storage Temperature	-10C to 70C (14F to 158F)
Humidity	10%-85% RH

Physical Characteristics

Color	Black
Form Factor	Attached Cable
Material	Plastic
Product Length	9.3 in [23.5 cm]
Product Width	1.1 in [2.7 cm]
Product Height	0.6 in [1.5 cm]
Weight of Product	0.9 oz [25.0 g]

Packaging Information

Package Quantity	1
Package Length	8.7 in [22.0 cm]
Package Width	4.8 in [12.2 cm]
Package Height	0.6 in [1.6 cm]
Shipping (Package) Weight	1.1 oz [30.0 g]

What's in the Box

Included in Package	1 - USB-C to GbE network adapter
---------------------	----------------------------------

****Product appearance and specifications are subject to change without notice.***