

USB 2.0 Extender over Cat5/Cat5e/Cat6 Ethernet Cable (RJ45) - 330ft/100m Industrial USB Extender Adapter Kit w/ ESD Protection & Metal Case - Externally Powered - 480 Mbps

Product ID: USB2001EXT2NA



The USB2001EXTNA USB 2.0 extender over ethernet lets you extend a USB 2.0 connection over distances of up to 100-meters (330-feet), over standard Cat5e or Cat6 ethernet LAN cabling.

With data bandwidth of up to 480 Mbps and no software installation required, the USB extender over Cat5e, Cat6, or Cat7 offers a fast, easy, and versatile solution for business or industrial applications with durable metal housing, an included surface-mounting bracket kit and simple plug-and-play installation.

Plus, the 100m USB extender provides up to the full 500 mA of power (with the use of an external power adapter at the remote end) allowing for greater compatibility with bus-powered USB devices.

Connecting older peripherals isn't a problem. This versatile USB over network extender is backward compatible with legacy USB 1.0 devices. The USB over ethernet hub enables almost any kind of USB device to be placed at remote locations away from the host computer.

StarTech.com conducts thorough compatibility and performance testing on all our products to ensure we are meeting or exceeding industry standards and providing high-quality products to IT Professionals. Our local StarTech.com Technical Advisors have broad product expertise and work directly with our StarTech.com Engineers to provide support for our customers both pre and post-sales

The USB2001EXT2NA is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility





Applications

- Perfect for environments where the host computer is in an inaccessible location
- No need to run new wiring, you can extend USB connections between rooms using existing direct, in-wall Cat5, Cat6, or Cat7 cable
- Use as a mid-point repeater to increase the connection distance of your USB peripheral and to reduce cable clutter

Features

- **USB EXTENDER:** Extend 1x USB 2.0 connection up to 100m (330ft) over CAT5/CAT6 cable w/ data transfer rates up to 480Mbps; LEDs monitor connectivity incl Power, Link, Host & Activity status; Newer version of USB2001EXT2
- **CONNECT REMOTE USB DEVICES:** USB extenders are ideal to remotely access USB devices like printers, cameras, plotters, keyboard/mouse, laser cutters, displays, or CCTV systems from a convenient location
- **INDUSTRIAL USB EXTENDER:** Built w/ durable extruded aluminum construction for high wear & tear environments w/ mounting brackets incl; provides 8kV/16kV Contact/Air Electrostatic Discharge protection
- **POWERED USB EXTENDER KIT:** The USB extender over Cat5/Cat6 cable (RJ45) incl. a power adapter & provides 5V, 500mA to the remote USB port, while powering the local transmitter from the PC USB port
- **PLUG-AND-PLAY:** The extender features driverless installation & is compatible w/ major operating systems incl. Windows, macOS, Linux; Backwards compatible with USB 1.0 and USB 1.1 devices

Hardware

Warranty	2 Years
Ports	1
Cabling	Cat 5e UTP or better

Performance

Maximum Data Transfer Rate	480 Mbps
Max Distance	100 m / 330 ft

Connector(s)

Local Unit Connectors	1 - USB B (4 pin)
	1 - RJ-45

Remote Unit Connectors	1 - USB 2.0 Type-A (4 pin, 480Mbps)
	1 - RJ-45

Software

OS Compatibility	OS Independent; No additional drivers or software required
------------------	--

Special Notes / Requirements

System and Cable Requirements	USB enabled computer system with available USB port
-------------------------------	---

Indicators

LED Indicators	1 - Activity
	1 - USB Link
	1 - Power
	1 - Host Connection
	1 - Link

Power

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	0.6A
Output Voltage	5 DC
Output Current	3A
Plug Type	C
Power Consumption (In Watts)	18

Environmental

Operating Temperature	0C to 50C (32F to 122F)
Storage Temperature	-20C to 70C (-4F to 158F)
Humidity	20~90% RH

Physical

Characteristics

Color	Black
Material	Aluminum
Product Length	3.3 in [8.5 cm]
Product Width	3.0 in [7.5 cm]
Product Height	1.0 in [2.6 cm]
Weight of Product	4.4 oz [125.0 g]

Packaging Information

Package Quantity	1
Package Length	9.6 in [24.4 cm]
Package Width	7.8 in [19.8 cm]
Package Height	3.1 in [7.8 cm]
Shipping (Package) Weight	1.9 lb [0.9 kg]

What's in the Box

Included in Package	1 - Local Unit
	1 - Remote Unit
	1 - 5.6 ft [170 cm] USB 2.0 Cable
	1 - Mounting Kit
	1 - Universal Power Adapter with 5.6 ft [170 cm] Cable
	1 - 6 ft [180 cm] North America Power Cord
	1 - Quick Start Guide

****Product appearance and specifications are subject to change without notice.***