

2 Port 2-to-1 USB 3.0 Peripheral Sharing Switch – USB Powered

Produkt ID: USB221SS



The USB221SS 2-to-1 USB 3.0 Peripheral Sharing Switch lets you share a single USB 3.0 peripheral with 2 different computer systems, avoiding the cost of purchasing duplicate peripherals or the hassle of swapping cables from one system to another.

The USB sharing switch delivers speed and flexibility, with simple push-button controls for switching between computers, and support for SuperSpeed USB bandwidth (up to 5 Gbps) ensuring fast data transfers to/from your shared peripheral device. The switch is also backward compatible with USB 2.0/1.1 (480Mbps, 12Mbps respectively), so you don't have to worry about your computer or older peripherals not performing.

The 2-port USB switch can also be connected to a USB hub, to expand the number of devices you can share between the two connected systems, or to a USB drive enclosure or docking station, for a shared external storage solution.

The switch features a compact design that takes up minimal desk space and is USB-powered, so it doesn't require an AC wall outlet.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifikat, rapporter och kompatibilitet





Användning

- Share a USB printer or All-in-One between 2 local computers
- Switch a USB 3.0 peripheral between 2 computers on a work bench
- Connect an external hard drive between the two systems for merging data to a single shared drive

Funktioner

- USB 3.0 data transfer rates up to 5 Gbps
- Push-button controls for switching between computers
- Connect a USB hub to share additional peripherals
- USB-Powered, no additional power adapter or wall outlet required
- Includes 2 USB A-B cables for PC to switch connection
- Compact design
- Plug-and-Play, no software or drivers required

Hårdvara

Garantipolicy	2 Years
USB-C-enhetsport(ar)	Nej
USB-C-värdanslutning	Nej
Snabbladdningsport(ar)	Nej
Portar	2
Busstyp	USB 3.2 Gen 1 (5 Gbps)

Prestanda

Maximal dataöverföringshastighet	5 Gbps
----------------------------------	--------

	Maximal kabellängd	4.9 ft [1.5 m]
	Typ och hastighet	USB 3.0 - 5 Gbit/s
Kontakt(er)	Externa portar	1 - USB Type-A (9-stifts) USB 3.0 (5 Gbps) 2 - USB 3.2 Type-B (9 stift, Gen 1, 5 Gbps)
Mjukvara	OS-kompatibilitet	OS Independent - No software or drivers required
Särskilda anmärkningar/krav	Obs.	The total cable length from host system to your connected peripheral should not exceed 2.5m (8.2ft)
Indikatorer	LED-indikatorer	2 - Computer selection indicators
Ström	Strömkälla	Strömförsörjd via USB
	Inspänning	5V DC
	Utspänning	5 DC
Miljö	Drifttemperatur	0°C to 40°C (32°F to 104°F)
	Förvaringstemperatur	-20°C to 60°C (-4°F to 140°F)
	Luftfuktighet	0~80% RH
Utseende	Färg	Svart
	Formfaktor	Kompakt
	Kabinettyp	Av plast
	Produktlängd	2.7 in [6.9 cm]
	Produktbredd	1.7 in [4.2 cm]

Produkthöjd 0.9 in [2.2 cm]

Produktvikt 1.4 oz [40.0 g]

Förpackning

Förpackningsantal 1

Paketets längd 5.2 in [13.1 cm]

Paketets bredd 6.4 in [16.2 cm]

Paketets höjd 1.7 in [4.3 cm]

Fraktvikt (förpackning) 8.1 oz [229.0 g]

Vad det är i lådan

Ingår i paketet 1 - USB 3.0 Sharing Switch

2 - 1m USB 3.0 A-B Cables

1 - Instruction Manual

Warranty Information

Warranty 2 År

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.