

2U skjutbar serverrackhylla - 51 till 76 cm justerbart monteringsdjup - Ventilerad - 23 kg - Kraftig universell 19-tums rackhylla för utrustningsrack - 61 cm djup

Produkt ID: UNISLDSHF19



The UNISLDSHF19 19in Vented Adjustable Mounting Depth Sliding Server Rack Cabinet Shelf offers a simple way to install non rack mountable equipment into a server cabinet or open server rack. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

Offering a weight capacity of up to 50 lbs (22.7 kg), the sliding rack shelf features a ventilated, cold-rolled steel shelf on two locking adjustable rails which allow the shelf to be installed into cabinets or racks with mounting depths from 20in (510mm) to 30in (744mm). The locking feature locks the shelf 3/4 of the way out, preventing the shelf from accidentally falling out of the rack or sliding back in before maintenance is complete.

Backed by a StarTech.com lifetime warranty.

Certifikat, rapporter och kompatibilitet

Användning

- For use with all 19" wide Server Racks and Cabinets
- Add a sliding rack mounting option for non rack mountable equipment

Funktioner

- Constructed from 16 gauge cold rolled steel

- Highly ventilated to reduce airflow impedance
- TAA compliant for GSA Schedule purchases
- Supports up to 22.7 kg (50 lbs) of equipment
- Meets EIA RS-310-C standards
- Locking rails prevent the shelf from sliding all the way out
- Includes Mounting screws and nuts

Hårdvara

Garantipolicy	Lifetime
Ramtyp	Stål
U-höjd	2U
Kabelhantering	Nej
Industristandarder	EIA RS310-C

Prestanda

Weight Capacity (Stationary)	50.1 lb [22.7 kg]
------------------------------	-------------------

Utseende

Färg	Svart
Kabinettyp	Stål
Produktlängd	24.0 in [61.0 cm]
Produktbredd	17.8 in [45.2 cm]
Produkt höjd	1.8 in [45.0 mm]
Produktvikt	14.1 lb [6.4 kg]
Maximalt monteringsdjup	29.3 in [74.4 cm]
Minsta monteringsdjup	20.1 in [51.0 cm]

Förpackning

Package Length	26.8 in [68.0 cm]
Package Width	20.7 in [52.7 cm]
Package Height	5.4 in [13.8 cm]
Fraktvikt (förpackning)	18.5 lb [8.4 kg]

Vad det är i lådan

Ingår i paketet	Sliding Shelf
	M6 Screws
	M6 Cage Nuts

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

