

## 2 Port 2-to-1 USB 3.0 Peripheral Sharing Switch – USB Powered

**Product ID:** USB221SS



The USB221SS 2-to-1 USB 3.0 Peripheral Sharing Switch lets you share a single USB 3.0 peripheral with 2 different computer systems, avoiding the cost of purchasing duplicate peripherals or the hassle of swapping cables from one system to another.

The USB sharing switch delivers speed and flexibility, with simple push-button controls for switching between computers, and support for SuperSpeed USB bandwidth (up to 5 Gbps) ensuring fast data transfers to/from your shared peripheral device. The switch is also backward compatible with USB 2.0/1.1 (480Mbps, 12Mbps respectively), so you don't have to worry about your computer or older peripherals not performing.

The 2-port USB switch can also be connected to a USB hub, to expand the number of devices you can share between the two connected systems, or to a USB drive enclosure or docking station, for a shared external storage solution.

The switch features a compact design that takes up minimal desk space and is USB-powered, so it doesn't require an AC wall outlet.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility

### Applications

- Share a USB printer or All-in-One between 2 local computers
- Switch a USB 3.0 peripheral between 2 computers on a work bench
- Connect an external hard drive between the two systems for merging data to a single shared drive

## Features

- USB 3.0 data transfer rates up to 5 Gbps
- Push-button controls for switching between computers
- Connect a USB hub to share additional peripherals
- USB-Powered, no additional power adapter or wall outlet required
- Includes 2 USB A-B cables for PC to switch connection
- Compact design
- Plug-and-Play, no software or drivers required

---

### Hardware

Warranty	2 Years
USB-C Device Port(s)	No
USB-C Host Connection	No
Fast-Charge Port(s)	No
Ports	2
Bus Type	USB 3.0

---

### Performance

Maximum Data Transfer Rate	5 Gbps
Maximum Cable Length	4.9 ft [1.5 m]
Type and Rate	USB 3.0 - 5 Gbit/s

---

### Connector(s)

External Ports	USB Type-A (9 pin) USB 3.0 (5 Gbps) USB Type-B (9 pin) USB 3.0
----------------	---


---

### Software

OS Compatibility	OS Independent - No software or drivers required
------------------	--

---

### Special Notes / Requirements



Note	The total cable length from host system to your connected peripheral should not exceed 2.5m (8.2ft)
------	---

---

**Indicators**

LED Indicators	Computer selection indicators
----------------	-------------------------------

---

**Power**

Power Source	USB-Powered
--------------	-------------

---

**Environmental**

Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-20C to 60C (-4F to 140F)
Humidity	0~80% RH

---

**Physical Characteristics**

Color	Black
Form Factor	Compact
Material	Plastic
Product Length	2.7 in [69.0 mm]
Product Width	1.7 in [42.0 mm]
Product Height	0.9 in [22.0 mm]
Weight of Product	1.4 oz [40.0 g]

---

**Packaging Information**

Package Length	5.2 in [13.1 cm]
Package Width	6.4 in [16.2 cm]
Package Height	1.7 in [43.0 mm]
Shipping (Package) Weight	8.1 oz [229.0 g]

---

**What's in the Box**

Included in Package	USB 3.0 Sharing Switch
	1m USB 3.0 A-B Cables



Instruction Manual

---

***\*Product appearance and specifications are subject to change without notice.***

