

USB-C to USB-C Cable w/ 5A PD - M/M - 1 m (3 ft.) - USB 2.0 - USB-IF Certified

Product ID: USB2C5C1M



With up to 5A (100W) of power output, you can use this USB-C to USB-C cable to power and charge a USB-C laptop, such as your Apple MacBook Pro, MacBook or Chromebook Pixel, using a USB-C wall charger, car charger or power bank. Or, you can power your laptop from a USB-C docking station.

The 5A of Power Delivery lets you charge your mobile devices faster than with a regular USB-C 2.0 cable, which is perfect for people on the move. Decrease your charge times and make sure your mobile devices are ready, whenever you need them while you're on the road.

The USB Type-C cable has undergone rigorous compliance testing and is certified by USB-IF (USB Implementers Forum) to meet all USB 2.0 specifications. This includes all environmental, electrical and mechanical standards, which ensures a reliable and high-quality cable for all of your USB-C devices.

The USB2C5C1M from StarTech.com is backed by a 2-year warranty for guaranteed reliability.

Certifications, Reports and Compatibility

Applications

- Power your USB-C laptop from a charger or power bank
- Charge your USB-C laptop from a docking station
- Fast-charge your USB-C mobile devices from a charger
- Sync your USB-C mobile devices with a laptop

Features

- USB-IF Certified
- Provides up to 5 amps of power output for fast charging your mobile devices, or powering your USB-C laptop
- Thunderbolt 3 port compatible
- Guaranteed reliability with our 2-year warranty

Hardware

Warranty	2 Years
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

Performance

Type and Rate	USB 2.0 - 480 Mbit/s
---------------	----------------------

Connector(s)

Connector A	USB Type-C (24-pin) USB 2.0 (480Mbps)
Connector B	USB Type-C (24-pin) USB 2.0 (480Mbps)

Power

Power Delivery	100W
----------------	------

Physical Characteristics

Color	Black
Connector Style	Straight
Wire Gauge	24/26 AWG
Cable Length	39.4 in [100 cm]
Product Length	39.4 in [100 cm]
Product Width	0.4 in [10 mm]
Product Height	0.2 in [6 mm]
Weight of Product	1.0 oz [29 g]

**Packaging
Information**

Package Length	8.9 in [22.5 cm]
Package Width	4.9 in [12.5 cm]
Package Height	0.4 in [10 mm]
Shipping (Package) Weight	1.2 oz [34 g]

**What's in the
Box**

Included in Package	USB-C cable
---------------------	-------------

****Product appearance and specifications are subject to change without notice.***

