

## USB-C to USB-C Cable w/ 5A PD - M/M - White - 4 m (13 ft.) - USB 2.0 - USB-IF Certified

Product ID: USB2C5C4MW



With up to 5A (100W) of power output, you can use this USB-C to USB-C cable to power and charge a USB-C laptop, such as your Apple MacBook Pro, MacBook or Chromebook Pixel, using a USB-C wall charger, car charger or power bank. Or, you can power your laptop from a USB-C docking station.

The 5A of Power Delivery lets you charge your mobile devices faster than with a regular USB-C 2.0 cable, which is perfect for people on the move. Decrease your charge times and make sure your mobile devices are ready whenever you need them while you're on the road.

The long cable lets you overcome distance restrictions and stay connected. You can take notes in a boardroom, catch up on emails in your hotel room, or read in a coffee shop.

The USB Type-C cable has undergone rigorous compliance testing and is certified by USB-IF (USB Implementers Forum) to meet all USB 2.0 specifications. This includes all environmental, electrical and mechanical standards, which ensures a reliable and high-quality cable for all of your USB-C devices.

The USB2C5C4MW from StarTech.com is backed by a 2-year warranty for guaranteed reliability.

### Certifications, Reports and Compatibility



### Applications

- Power your USB-C laptop from a charger or power bank
- Charge your USB-C laptop from a docking station
- Fast-charge your USB-C mobile devices from a charger
- Sync your USB-C mobile devices with a laptop

## Features

- USB-IF Certified
- Power your USB-C laptop or fast-charge your mobile devices, with up to 5 amps of power output
- White cable complements your Apple MacBook
- Thunderbolt 3 port compatible
- Guaranteed reliability with our 2-year warranty

<b>Hardware</b>	Warranty	2 Years
	Connector Plating	Nickel
	Cable Jacket Material	PVC - Polyvinyl Chloride
	Cable Shield Material	Aluminum-Mylar Foil with Braid
<b>Performance</b>	Type and Rate	USB 2.0 - 480 Mbit/s
<b>Connector(s)</b>	Connector A	USB Type-C (24-pin) USB 2.0 (480Mbps)
	Connector B	USB Type-C (24-pin) USB 2.0 (480Mbps)
<b>Power</b>	Power Delivery	100W
<b>Physical Characteristics</b>	Color	White
	Connector Style	Straight
	Wire Gauge	24/26 AWG
	Cable Length	13.1 ft [4 m]
	Product Length	13.1 ft [4.0 m]
	Product Width	0.5 in [12.000 mm]
	Product Height	0.4 in [10.000 mm]
	Weight of Product	7.1 oz [200.000 g]
<b>Packaging Information</b>	Package Length	8.7 in [2.2 cm]
	Package Width	7.9 in [2.0 cm]
	Package Height	0.4 in [10.000 mm]
	Shipping (Package) Weight	7.3 oz [208.000 g]
<b>What's in the Box</b>	Included in Package	USB-C cable

*\*Product appearance and specifications are subject to change without notice.*

