

USB-C Cable - M/M - 1 m (3 ft.) - USB 2.0 - USB-IF Certified

Product ID: USB2CC1M



This USB-C to USB-C cable lets you charge and sync your USB Type-C devices. It's also compatible with Thunderbolt 3 ports.

Connect your newer USB-C mobile devices, such as the Samsung Galaxy S8, S8+, Nexus 6P, and 5X phones, to your computer. The cable delivers up to a 3 amp charge, and supports data transfer speeds of up to 480Mbps.

With up to 3A of power output, this USB Type-C cable can also be used to power a USB-C laptop, such as your Apple MacBook or Chromebook Pixel. Simply connect your laptop to your USB-C wall charger.

Replace the cable that came with your device, or keep one as a spare while you're traveling, so that all of your devices will be ready to use whenever you need them while you're on the road.

The USB Type-C connector is smaller and easier to use than previous USB connectors. With a reversible design, you can plug it into your devices with either side facing up. Insert the cable the right way every time - no more frustration or port damage.

This USB-C cable has been certified with USB-IF (USB Implementers Forum) in order to meet all USB 2.0 specifications. This includes all environmental, electrical and mechanical standards set by USB compliance. This ensures a high-quality, reliable cable for all your USB-C devices.

The USB2CC1M from StarTech.com is backed by a lifetime warranty for guaranteed reliability.

Certifications, Reports and Compatibility



Applications

- Power your USB-C enabled laptops with a USB Type-C wall charger
- Charge your USB-C mobile devices with USB-C computer or wall charger
- Sync your USB-C devices with a USB-C computer

Features

- Connect more easily with reversible USB Type-C connectors, which can plug into your devices with either side facing up
- Thunderbolt 3 port compatible
- Guaranteed reliability with our lifetime warranty
- USB-IF Certified

Hardware	Warranty	Lifetime
	Connector Plating	Nickel
	Cable Jacket Material	PVC - Polyvinyl Chloride
	Cable Shield Material	Aluminum-Mylar Foil with Braid
Performance	Type and Rate	USB 2.0 - 480 Mbit/s
Connector(s)	Connector A	USB Type-C (24-pin) USB 2.0 (480Mbps)
	Connector B	USB Type-C (24-pin) USB 2.0 (480Mbps)
Power	Power Delivery	100W
Physical Characteristics	Color	Black
	Connector Style	Straight
	Wire Gauge	22/30 AWG
	Cable Length	39.4 in [10 cm]
	Product Length	39.4 in [10 cm]
	Weight of Product	0.9 oz [26 g]
Packaging Information	Package Quantity	1
	Package Length	8.9 in [2.2 cm]
	Package Width	4.9 in [1.2 cm]
	Package Height	0.2 in [6 mm]
	Shipping (Package) Weight	1.1 oz [31 g]
What's in the	Included in Package	1m (3ft) USB 2.0 USB-C Cable - M/M

Box

**Product appearance and specifications are subject to change without notice.*

