

USB-C Cable with Power Delivery (5A) - M/M - 4 m (13 ft.) - USB 2.0 - USB-IF Certified

Product ID: USB2C5C4M



This USB-C cable with USB Power Delivery lets you power USB Type-C devices from your USB-C laptop or charge your USB-C laptop from a USB-C wall charger.

With up to 5A (100W) of power output, you can use this USB Type-C cable to power and charge a USB-C laptop, such as your Apple MacBook or Chromebook Pixel, using a USB-C wall charger, car charger or power bank. Or, you can power your laptop from a USB-C docking station.

The 5A of power delivery lets you charge your mobile devices faster than with a regular USB-C 2.0 cable. The cable is perfect for people on the move - decrease your charge times and make sure your mobile devices are ready, whenever you need them, while you're on the road.

The non-standard 4-meter cable gives you the extra length you need to overcome distance restrictions and stay connected. You can charge and sync your USB-C mobile device, in almost any environment. Even while you're taking notes in a boardroom, catching up on emails in your hotel room, or reading in a coffee shop, the connection to your mobile device will reach your computer or wall charger more comfortably.

The cable has undergone rigorous compliance testing and is certified by USB-IF (USB Implementers Forum) to meet all USB 2.0 specifications. This includes all environmental, electrical and mechanical standards, which ensures a reliable and high-quality cable for all of your USB-C devices.

The USB2C5C4M from StarTech.com is backed by a 2-year warranty for guaranteed reliability.

Certifications, Reports and Compatibility



Applications

- Power your USB-C laptop from a USB Type-C wall charger, car charger or power bank
- Charge your USB Type-C laptop from a your docking station
- Fast charge your USB-C mobile devices from your USB-C laptop or wall charger
- Sync your USB-C mobile devices with your USB-C computer

Features

- USB-IF Certified
- Provides up to 5 amps of power output for fast charging your mobile devices, or powering your USB-C laptop
- Offers 4 meters in cable length
- Thunderbolt 3 port compatible
- Guaranteed reliability with our 2-year warranty

Hardware	Warranty	2 Years
	Connector Plating	Nickel
	Cable Jacket Material	PVC - Polyvinyl Chloride
	Cable Shield Material	Aluminum-Mylar Foil with Braid
Performance	Type and Rate	USB 2.0 - 480 Mbit/s
Connector(s)	Connector A	USB Type-C (24-pin) USB 2.0 (480Mbps)
	Connector B	USB Type-C (24-pin) USB 2.0 (480Mbps)
Power	Power Delivery	100W
Physical Characteristics	Color	Black
	Connector Style	Straight
	Wire Gauge	24/26 AWG
	Cable Length	13.1 ft [4 m]
	Product Length	13.1 ft [4 m]
	Weight of Product	7.7 oz [219 g]
Packaging Information	Package Length	8.7 in [2.2 cm]
	Package Width	7.9 in [2 cm]
	Package Height	1.1 in [28 mm]
	Shipping (Package) Weight	8.1 oz [229 g]
What's in the Box	Included in Package	USB-C cable

****Product appearance and specifications are subject to change without notice.***

