

Right-Angle USB-C Cable - M/M - 1 m (3 ft.) - USB 2.0

Product ID: USB2CC1MR



This right-angle USB-C cable is great for charging your mobile devices in a car, or for accessing your phone or tablet while it's connected to a wall charger or laptop. The cable can also be used for charging your laptop from an AC charger.

The cable features a right-angled USB Type-C connector that lets you connect to ports that are difficult to reach, which is perfect for charging your car-mounted mobile devices.

If you want to use your mobile device while it's charging, you can position the cable to the left or right of your device, in either portrait or landscape mode. Even while you're charging your mobile device, you can use it to text, work or game, without the cable getting in the way.

The angled connector also prevents the cable from bending awkwardly or from straining too much to make a connection. It offers a more natural fit at the connection point, preventing unnecessary stress and damage to the cable and device port.

With up to 3A of power output, you can use this USB Type-C cable to power a USB-C laptop, such as your Apple MacBook or Chromebook Pixel. Simply connect the cable to your USB-C laptop and to a USB-C wall charger.

Replace the USB-C cable that came with your mobile device, or keep one as a spare while traveling so that your mobile devices and laptop will be ready to use while you're on the road.

The USB2CC1MR from StarTech.com is backed by a lifetime warranty for guaranteed reliability.

Certifications, Reports and Compatibility

Applications

- Power your USB-C enabled laptops with a USB Type-C wall charger

- Charge and sync your USB-C mobile digital devices from the USB-C port on your laptop
- Charge your USB-C devices using a USB-C wall charger, car charger or power bank

Features

- Right-angle USB-C connector that lets you connect to your device even in hard-to-reach areas
- Thunderbolt 3 port compatible
- Guaranteed reliability with our lifetime warranty

Hardware

Warranty	Lifetime
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

Performance

Type and Rate	USB 2.0 - 480 Mbit/s
---------------	----------------------

Connector(s)

Connector A	USB Type-C (24-pin) USB 2.0 (480Mbps)
Connector B	USB Type-C (24-pin) USB 2.0 (480Mbps)

Power

Power Delivery	60W
----------------	-----

Physical Characteristics

Color	Black
Connector Style	Straight to Right Angle
Wire Gauge	22/30 AWG
Cable Length	39.4 in [100 cm]
Product Length	39.4 in [100.0 cm]
Product Width	0.4 in [11.0 mm]



Product Height	0.2 in [6.0 mm]
Weight of Product	1.1 oz [30.0 g]

Packaging Information

Package Length	8.9 in [22.5 cm]
Package Width	4.9 in [12.5 cm]
Package Height	0.4 in [10.0 mm]
Shipping (Package) Weight	1.3 oz [37.0 g]

What's in the Box

Included in Package	USB-C cable
---------------------	-------------

****Product appearance and specifications are subject to change without notice.***

