USB DVI External Dual or Multi Monitor Video Adapter

ID prodotto: USB2DVI

The USB2DVI USB DVI Multi Monitor External Video Adapter turns an available USB 2.0 port into an external video card DVI port - providing high quality dual-display or multi-monitor capability that can be used in a variety of laptop or desktop applications to increase your productivity.

The device also offers the option of running up to five additional displays simultaneously (using five USB2DVI Multi Monitor External Video Cards). Each connected adapter can be used to further extend the desktop or mirror the image shown on the existing display - all without having to open the computer case to install an additional video card.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certificazioni, report e compatibilità

RoHS Compliant

Windows 8

Windows 7

macOS Monterey

macOS Big Sur

Applicazioni

• Add a secondary display adapter and extend your desktop display without taking apart your computer to install a new video card

• Add multiple (up to five) monitors / projectors to your computer setup using one USB2DVI device for each additional display

• View large or multiple spreadsheets across multiple displays

• A compact, lightweight solution for traveling business associates using laptop PCs enabling connection to a secondary display

• Connect multiple monitors to a single computer to create engaging multimedia presentations

• Use the adapter to connect your PC to your television for showing family pictures and movies

• Increase productivity by running multiple applications on different screens, check your email on one display and work on a document in the other

• Great for researchers and writers offering the ability to have reference material on one display and a working document copy on the other

Caratteristiche

• Optimal performance at 1680x1050 and ideal for use with 20" to 22" monitors or smaller

• Acts as an external video card connected through USB 2.0

• No power adapter required

• Quick and easy installation

• Supports the use of DVI to VGA or DVI to HDMI adapters

Hardware		
	Norme di garanzia	2 Years
	Ingresso AV	USB 2.0
	Uscita AV	DVI
	Pass-through USB	No
	Memoria	16MB
	ID chipset	DisplayLink - DL-165
Prestazioni		
	Risoluzioni digitali massime	1600x1200(standard) or 1680x1050(wide) @ 32 bits

	Risoluzioni supportate	Widescreen (16/32 bit): 1680x1050, 1440x900, 1366x768 Standard (16/32 bit): 1600x1200, 1280x1024, 1280x960, 1024x768, 800x600, 640x480
	Specifiche generali	This USB video adapter uses a DisplayLink family chipset. If you’re connecting this device to a computer along with additional USB video adapters or docking stations, please avoid using devices with a Trigger or Fresco family chipset.
Connettore/i		
	Connettore A	1 - USB 2.0 Tipo-A (4 pin, 480Mbps)
	Connettore B	1 - DVI-I (29 pin)
Software		
	Compatibilità con sistemi operativi	Windows® XP (32 bit)/Vista (32/64 bit)/7 (32/64 bit)/8 (32/64 bit)*, interfaccia Aero 3D supportata macOS Monterey (12.0) macOS Ventura (13.0) macOS Sonoma (14.0) /macOS Big Sur (11.0)/Mountain Lion (10.8)/Lion (10.7)/Snow Leopard (10.6)/Leopard (10.5)/Tiger (10.4)
Note/requisiti speciali		
	Requisiti di sistema e cavi	Porta USB 2.0 disponibile CPU da 1,2 GHz o superiore RAM 512 MB Spazio su disco rigido 30 MB
	Nota	Attualmente l'alimentazione di computer Macintosh basati su PC, come gli ultimi modelli di iMac, PowerBook e PowerMac, non è supportata This USB video adapter uses a DisplayLink® family

		chipset. If you’re connecting this device to a computer along with additional USB video adapters or docking stations, avoid using devices with different family chipsets, such as Trigger or Fresco Logic®
		Connect a maximum of five USB video adapters on a single computer. Support for multiple adapters will vary depending upon your system resources
		This USB video adapter is not intended for graphical intensive applications, such as gaming
Caratteristiche fisiche		
	Colore	Nero
	Lunghezza cavo	19.7 in [500 mm]
	Lunghezza prodotto	3.5 in [90 mm]
	Larghezza prodotto	1.9 in [4.8 cm]
	Altezza prodotto	0.9 in [2.4 cm]
	Peso prodotto	2.6 oz [73 g]
Informazioni confezione		
	Package Length	5.7 in [14.6 cm]
	Package Width	1.9 in [47 mm]
	Package Height	8.0 in [20.2 cm]
	Peso spedizione (confezione)	6.4 oz [180.0 g]
Contenuto della confezione		
	Incluso nella confezione	1 - Adattatore USB a DVI
		1 - CD con i driver
		1 - Manuale di istruzioni

* L'aspetto e le specifiche dell'articolo sono soggetti a modifiche senza preavviso.