

USB-C Cable - M/M - 2 m (6 ft.) - USB 2.0 - USB-IF Certified

**Product ID:** USB2CC2M



This USB-C to USB-C cable makes it easy to charge and sync USB Type-C devices, such as the Samsung Galaxy S8, S8+, Nexus 6P, and 5X phones, using the USB-C port on your computer.

The cable is also compatible with Thunderbolt 3 ports, which means you can charge and sync your USB-C mobile devices using your Thunderbolt 3 laptop.

The 2-meter cable gives you the extra length you need to overcome distance restrictions and stay connected. You can charge and sync your USB-C mobile device, in almost any environment. Even while you're taking notes in a boardroom, catching up on emails in your hotel room, or reading in a coffee shop, your mobile device will reach your computer or wall charger more comfortably.

With up to 3A of power output, you can use this USB Type-C cable to power a USB-C laptop, such as your Apple MacBook or Chromebook Pixel. Simply connect the cable to your USB-C laptop and to a USB-C wall charger.

Replace the USB-C cable that came with your device, or keep one as a spare while you're traveling, so that all of your devices will be ready to use whenever you need them while you're on the road.

The cable has undergone rigorous compliance testing and is certified by USB-IF (USB Implementers Forum) to meet all USB 2.0 specifications. This includes all environmental, electrical and mechanical standards, ensuring a reliable, high-quality cable for all of your USB-C devices.

The USB2CC2M from StarTech.com is backed by a lifetime warranty for guaranteed reliability.

## **Certifications, Reports and Compatibility**

### **Applications**

- Charge and sync your USB-C mobile digital devices from the USB-C port on your laptop

- Charge your USB-C devices using a USB-C wall charger

## Features

- USB-IF Certified
- Guaranteed reliability with our lifetime warranty
- Convenient, reversible USB-C connector makes every connection easy

---

### Hardware

Warranty	Lifetime
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

---

### Performance

Type and Rate	USB 2.0 - 480 Mbit/s
---------------	----------------------

---

### Connector(s)

Connector A	USB Type-C (24-pin) USB 2.0 (480Mbps)
Connector B	USB Type-C (24-pin) USB 2.0 (480Mbps)

---

### Power

Power Delivery	60W
----------------	-----

---

### Physical Characteristics

Color	Black
Connector Style	Straight
Wire Gauge	22/30 AWG
Cable Length	6.6 ft [2 m]
Product Length	6.6 ft [2.0 m]
Product Width	0.0 in [0.0 mm]
Product Height	0.0 in [0.0 mm]



Weight of Product	1.5 oz [42.0 g]
-------------------	-----------------

---

**Packaging Information**

Package Length	8.9 in [22.5 cm]
----------------	------------------

Package Width	4.9 in [12.5 cm]
---------------	------------------

Package Height	0.4 in [11.0 mm]
----------------	------------------

Shipping (Package) Weight	1.7 oz [47.0 g]
---------------------------	-----------------

---

**What's in the Box**

Included in Package	2m USB-C cable - USB 2.0
---------------------	--------------------------

---

***\*Product appearance and specifications are subject to change without notice.***

