

USB DVI External Dual or Multi Monitor Video Adapter

ID prodotto: USB2DVI



The USB2DVI USB DVI Multi Monitor External Video Adapter turns an available USB 2.0 port into an external video card DVI port - providing high quality dual-display or multi-monitor capability that can be used in a variety of laptop or desktop applications to increase your productivity.

The device also offers the option of running up to five additional displays simultaneously (using five USB2DVI Multi Monitor External Video Cards). Each connected adapter can be used to further extend the desktop or mirror the image shown on the existing display - all without having to open the computer case to install an additional video card.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certificazioni, report e compatibilità



Applicazioni

- Add a secondary display adapter and extend your desktop display without taking apart your computer to install a new video card

- Add multiple (up to five) monitors / projectors to your computer setup using one USB2DVI device for each additional display
- View large or multiple spreadsheets across multiple displays
- A compact, lightweight solution for traveling business associates using laptop PCs enabling connection to a secondary display
- Connect multiple monitors to a single computer to create engaging multimedia presentations
- Use the adapter to connect your PC to your television for showing family pictures and movies
- Increase productivity by running multiple applications on different screens, check your email on one display and work on a document in the other
- Great for researchers and writers offering the ability to have reference material on one display and a working document copy on the other

Caratteristiche

- Optimal performance at 1680x1050 and ideal for use with 20" to 22" monitors or smaller
- Acts as an external video card connected through USB 2.0
- No power adapter required
- Quick and easy installation
- Supports the use of DVI to VGA or DVI to HDMI adapters

Hardware

Norme di garanzia	2 Years
Ingresso AV	USB 2.0
Uscita AV	DVI
Pass-through USB	No
Memoria	16MB
ID chipset	DisplayLink - DL-165

Prestazioni

Risoluzioni digitali massime	1600x1200(standard) or 1680x1050(wide) @ 32 bits
------------------------------	--

Risoluzioni supportate	Widescreen (16/32 bit):
	1680x1050, 1440x900, 1366x768
	Standard (16/32 bit):
	1600x1200, 1280x1024, 1280x960, 1024x768, 800x600, 640x480
Specifiche generali	This USB video adapter uses a DisplayLink family chipset. If you're connecting this device to a computer along with additional USB video adapters or docking stations, please avoid using devices with a Trigger or Fresco family chipset.

Connettore/i

Connettore A	1 - USB 2.0 Tipo-A (4 pin, 480Mbps)
Connettore B	1 - DVI-I (29 pin)

Software

Compatibilità con sistemi operativi	Windows® XP (32 bit)/Vista (32/64 bit)/7 (32/64 bit)/8 (32/64 bit)*, interfaccia Aero 3D supportata
	macOS Monterey (12.0)
	macOS Ventura (13.0)
	macOS Sonoma (14.0)
	macOS Sequoia (15.0)
	/macOS Big Sur (11.0)/Mountain Lion (10.8)/Lion (10.7)/Snow Leopard (10.6)/Leopard (10.5)/Tiger (10.4)

Note/requisiti speciali

Requisiti di sistema e cavi	Porta USB 2.0 disponibile
	CPU da 1,2 GHz o superiore
	RAM 512 MB
	Spazio su disco rigido 30 MB
Nota	Attualmente l'alimentazione di computer Macintosh basati su PC, come gli ultimi modelli di iMac, PowerBook e PowerMac, non è supportata

This USB video adapter uses a DisplayLink® family chipset. If you're connecting this device to a computer along with additional USB video adapters or docking stations, avoid using devices with different family chipsets, such as Trigger or Fresco Logic®

Connect a maximum of five USB video adapters on a single computer. Support for multiple adapters will vary depending upon your system resources

This USB video adapter is not intended for graphical intensive applications, such as gaming

Caratteristiche fisiche

Colore	Nero
Lunghezza del cavo	19.7 in [500 mm]
Lunghezza prodotto	3.5 in [90 mm]
Larghezza prodotto	1.9 in [4.8 cm]
Altezza prodotto	0.9 in [2.4 cm]
Peso prodotto	2.6 oz [73 g]

Informazioni confezione

Lunghezza Confezione	5.7 in [14.6 cm]
Larghezza del Pacco	1.9 in [47 mm]
Altezza del Pacco	8.0 in [20.2 cm]
Peso spedizione (confezione)	6.4 oz [180.0 g]

Contenuto della confezione

Incluso nella confezione	1 - Adattatore USB a DVI
	1 - CD con i driver
	1 - Manuale di istruzioni

Informazioni sulla
garanzia

Warranty

2 Anni

* L'aspetto e le specifiche dell'articolo sono soggetti a modifiche senza preavviso.