

USB to DVI External Dual or Multi Monitor Video Adapter

Product ID: USB2DVIE2



The USB2DVIE2 USB DVI Multi Monitor External Video Adapter turns an available USB 2.0 port into an external video card DVI port - providing high quality dual-display or multi-monitor capability that can be used in a variety of laptop or desktop applications to increase your productivity.

The device also offers the option of running up to five additional displays simultaneously (using five USB2DVIE2 Multi Monitor External Video Cards). Each connected adapter can be used to further extend the desktop or mirror the image shown on the existing display - all without having to open the computer case to install an additional video card.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Add a secondary display adapter and extend your desktop display without taking apart your computer to install a new video card
- Add multiple (up to five) monitors / projectors to your computer setup using one USB2DVIE2 device for each additional display
- View large or multiple spreadsheets across multiple displays
- A compact, lightweight solution for traveling business associates using laptop PCs enabling connection to a secondary display
- Connect multiple monitors to a single computer to create engaging multimedia presentations
- Use the adapter to connect your PC to your television for showing family pictures and movies
- Increase productivity by running multiple applications on different screens, check your email on one display and work on a document in the other

- Great for researchers and writers offering the ability to have reference material on one display and a working document copy on the other

Features

- Includes easy to use software that allows for screen rotation, multi-display management and EDID monitor detection for increased compatibility with displays
- No power adapter required, easy installation
- Optimal performance at 1440x900 (higher resolutions supported) and ideal for use with 17" to 19" monitors or smaller
- Works with desktop and laptop computers
- Supports the use of DVI to VGA or DVI to HDMI adapters

Hardware	Warranty	2 Years
	AV Input	USB 2.0
	AV Output	DVI
	USB Pass-Through	No
	Memory	16MB
	Chipset ID	Trigger - Trigger 1+
Performance	Supported Resolutions	Widescreen(16/32 bit):
	General Specifications	1680x1050, 1440x900, 1280x800, 1280x768
		Standard(16/32 bit):
		1600x1200, 1400x1050, 1280x1024, 1280x960, 1152x864, 1024x768, 800x600
		This USB video adapter uses a Trigger family chipset. If you're connecting this device to a computer along with additional USB video adapters or docking stations, please avoid using devices with a DisplayLink or Fresco family chipset.
Connector(s)	Connector A	USB Type-A (4 pin) USB 2.0
	Connector B	DVI-I (29 pin)
Software	OS Compatibility	Windows 10 (32/64)
		Windows 8 / 8.1 (32/64)
		Windows 7(32/64)
		Windows Vista (32/64)
		Windows XP (32/64)

Special Notes / Requirements	System and Cable Requirements	System Processor: 1.2GHz
	Note	System Memory: 512MB
	Note	This USB video adapter uses a Trigger family chipset. If you're connecting this device to a computer along with additional USB video adapters or docking stations, avoid using devices with different family chipsets, such as DisplayLink or Fresco Logic
	Note	Connect a maximum of five USB video adapters on a single computer. Support for multiple adapters will vary depending upon your system resources
		This USB video adapter is not intended for graphical intensive applications, such as gaming

Physical Characteristics	Color	Black
	Product Length	3.6 in [91 mm]
	Product Width	2.1 in [53 mm]
	Product Height	0.7 in [18 mm]
	Weight of Product	3.8 oz [108 g]

Packaging Information	Package Length	8.3 in [21.1 cm]
	Package Width	5.7 in [14.5 cm]
	Package Height	1.6 in [40 mm]
	Shipping (Package) Weight	9.3 oz [263 g]

What's in the Box	Included in Package	Driver and Software CD
	Included in Package	USB to DVI Adapter
	Included in Package	Instruction Manual

****Product appearance and specifications are subject to change without notice.***

