

3.3ft (1m) USB-C Charging Cable, Charge & Sync, 240W (5A) PD EPR, USB 2.0 Laptop Charger Cable, USB-IF Certified , TPE Jacket - White USB C Charging Cord

**Product ID:** USB2EPR1MW



Connect a charger to a USB Power Delivery (PD) 3.1-enabled device, using this USB-C Charging Cable. The USB-C charger cord delivers up to 240W of Extended Power Range (EPR) Power Delivery and 5A output for fast charging. The connector markings enable quick visual identification, distinguishing this cable from other similar-looking or unmarked USB-C cables. Eliminate guesswork and always choose the appropriate Type-C cable to support full 240W charging.

#### Quality Construction

Designed for frequent use, the USB-C EPR Charging Cable features a rugged TPE outer jacket for increased wear resistance. The durable nickel-plated connectors are rated to operate beyond 10,000 insertion cycles, enhancing its durability and longevity.

#### Charge Mobile Devices On The Go

Charge a USB-C device with a USB-C wall charger, car charger, or power bank. The 1m (3.3ft) USB Type-C cable is the ideal length for desk and mobile workstations, commuters, in-car use or to reduce clutter when syncing with a USB-C laptop.

#### Power a Laptop

With up to 5A of output, the USB-C Charger Cord supports up to 240W of Power Delivery to charge a USB-C laptop, or fast charge a tablet or smartphone. To use, connect the cable from a USB-C laptop to a USB-C wall charger.

### Certifications, Reports and Compatibility



## Applications

- Ideal for high-power USB-C devices
- USB-IF Certified for guaranteed reliability

## Features

- **USB-C EPR CHARGING CABLE:** Type-C cable supports Power Delivery 3.1 Extended Power Range (EPR); Up to 240W to high-power USB-C laptops; Connect to a USB-C charger or hub; Connector markings identify data/power specs; Choose the right 240W cable at-a-glance
- **USB-IF CERTIFIED:** The USB C Cable is USB-IF certified with integrated E-marker chip, for consistent Power Delivery output to USB-C hosts and peripherals; When using certified cables, reliable performance and compatibility is guaranteed
- **QUALITY CONSTRUCTION:** Nickel-plated connectors rated beyond 10,000 insertion cycles; 30AWG wire tested to withstand 120° bends; Braided Aluminum shield for enhanced EMI protection; Durable TPE outer jacket is halogen-free and RoHS compliant
- **APPLICATIONS:** Compatible with USB-C Power Delivery-enabled devices; Ideal for high-power laptops requiring EPR charging, including 16in MacBook Pro M3 Pro/M3 Max; Supports USB 2.0 for general use, including file transfer and device synchronization
- **PERFORMANCE:** 240W/5A PD 3.1 EPR, 48V; Backward Compatible w/140W/100W/60W; USB 2.0 Type-C (480Mbps); 1-meter (3.3-foot) cable; Color: White; O.D.: 0.16in (4.0mm); TPE Jacket w/Braided Aluminum Shield; NOTE: USB-C video (DP Alt Mode) is not supported

---

### Hardware

Warranty	Lifetime
Active or Passive Adapter	Passive
Connector Plating	Nickel
Cable Jacket Material	TPE - Thermoplastic Elastomers
Cable Shield Material	Aluminum-Mylar Foil with Braid
Cable Type	Passive Copper Cable

---

### Performance

Maximum Data Transfer	480Mbps
-----------------------	---------

Rate	
Type and Rate	USB 2.0 - 480 Mbit/s
MTBF	Rated beyond 10,000 insertion cycles

---

**Connector(s)**

Connector A	1 - USB Type-C (24-pin) USB 2.0 (480Mbps)
Connector B	1 - USB Type-C (24-pin) USB 2.0 (480Mbps)

---

**Special Notes / Requirements**

Note	USB-C video (DP Alt Mode) is not supported
------	--

---

**Power**

Power Source	Bus Powered
Power Delivery	240W
Input Current	5A

---

**Environmental**

Operating Temperature	-10 to 60 (14&degF to 140&degF)
Storage Temperature	-20 to 70 (-4&degF to 158&degF)
Humidity	5%~85%

---

**Physical Characteristics**

Color	White
Connector Style	Straight
Wire Gauge	30 AWG
Material	Polyamide Resin
Cable Length	3.3 ft [1 m]
Cable OD	0.2 in [4 mm]
Product Length	3.3 ft [1.0 m]
Product Width	0.5 in [1.2 cm]
Product Height	0.3 in [6.4 mm]

Weight of Product	1.1 oz [32.0 g]
-------------------	-----------------

---

**Packaging Information**

Package Length	8.7 in [22.0 cm]
----------------	------------------

Package Width	5.0 in [12.7 cm]
---------------	------------------

Package Height	0.5 in [1.3 cm]
----------------	-----------------

Shipping (Package) Weight	1.3 oz [37.0 g]
---------------------------	-----------------

---

**What's in the Box**

Included in Package	1 - 1m USB-C Charging Cable M/M
---------------------	---------------------------------

---

***\*Product appearance and specifications are subject to change without notice.***