

USB 2.0 HD PVR Gaming and Video Capture Device – 1080p HDMI / Component

Product ID: USB2HDCAP



The USB2HDCAP USB 2.0 HD Video Capture Device lets you record high-definition (1080p) video and stereo audio from an HDMI, S-Video or Component source to your computer, through an available USB 2.0 port - the perfect solution for recording video game play, or home videos for editing and compiling.

This versatile USB capture device supports both NTSC and PAL systems, and includes an easy-to-use video capture software suite which lets you record video or take still screenshots and save them to your PC. The device also offers video pass-through, so you can watch the same source on an external display.

The capture device features on-board hardware H.264 encoding, which manages the video conversion process independently of your computer and in turn saves valuable system resources.

Please Note: This USB video capture device will not record digitally encrypted content.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Record and convert video from camcorders, game consoles or cameras, into digital format
- Import recorded videos into your computer system for editing, to make your own compilations
- HDMI/Component Screen Capture
- Create walkthroughs, how-to videos, tutorials, and/or presentations for educational, work-related, or entertainment purposes

- Build video data archives

Features

- Capture video from HDMI, Component, S-Video, or Composite input sources
- Supports 2-channel stereo audio (HDMI / RCA)
- 1080p Video Capture (HDMI and Component)
- NTSC and PAL systems supported
- 16:9 and 4:3 Aspect Ratio
- Still image capture supported
- Built-in H.264 and MPEG-4 hardware encoder
- Video Pass Through (HDMI / Component / S-Video)

Hardware

Warranty	2 Years
AV Input	Composite
	HDMI
	S-Video (4 pin, Mini-DIN) Female
	HDMI
	Component
AV Output	USB
	HDMI
	Component
	S-Video (4 pin, Mini-DIN) Female
Audio	Yes
Industry Standards	NTSC, PAL-M, PAL-60, PAL
	Video Encoding: MPEG4/H.264

Performance

Maximum Digital	1080p/30/50/60, Video Output at 1080p/30
-----------------	--

Resolutions

Supported Resolutions 1080i/p, 720p, 576i/p, 480i/p

Audio Specifications HDMI or Component RCA Stereo

Connector(s)

Connector A	USB B (4 pin)
	HDMI (19 pin)
	Component Video (3 x RCA)
	S-Video (4 pin, Mini-DIN)
	Stereo Audio (2 x RCA)
Connector B	HDMI (19 pin)
	Component Video (3 x RCA)
	Stereo Audio (2 x RCA)
	S-Video (4 pin, Mini-DIN)

Software

OS Compatibility Windows 10 (32/64), 8 / 8.1 (32/64bit), 7 (32/64bit), Vista (32/64), XP (32/64)

Special Notes / Requirements

System and Cable Requirements CPU: Intel Core2 Quad Q9400 2.66GHz
Memory : 512 MB
Video : 1024768, DirectX 9.0c Compatible Graphics Card

Indicators

LED Indicators USB (Power)
Video Source

Power

Power Source USB-Powered

Environmental

Operating Temperature 0C to 45C (32F to 113F)



Storage Temperature	-5C to 60C (23F to 140F)
Humidity	20%~80%

Physical Characteristics

Product Length	5.5 in [14 cm]
Product Width	3.5 in [90 mm]
Product Height	1.0 in [25 mm]
Weight of Product	5.3 oz [150 g]

Packaging Information

Package Length	8.7 in [22 cm]
Package Width	6.5 in [16.5 cm]
Package Height	2.4 in [60 mm]
Shipping (Package) Weight	19.1 oz [540 g]

What's in the Box

Included in Package	USB Capture Device
	Component Cable
	Driver / Software CD
	Instruction Manual
	USB Cable
	RCA Audio Cable

****Product appearance and specifications are subject to change without notice.***

