

USB to VGA Adapter - 1920x1200

Product ID: USB2VGAE3



The USB2VGAE3 USB VGA Multi-Monitor External Video Adapter lets you add a high-resolution (1920x1200) external VGA output to your desktop or laptop computer, using an available USB 2.0 port.

A cost-effective solution for systems that lack the outputs required for a multi-monitor setup, this high-performance USB to VGA adapter can be used to mirror your primary display and show the same image on both screens, or extend your desktop to double your workspace.

This small form factor USB video adapter can be used with up to 4 additional (5 total) USB2VGAE3 USB video adapters, creating multiple VGA connections to add displays quickly and easily - all without having to open the computer case to add extra video cards.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Add a secondary display adapter and extend your desktop display without taking apart your computer to install a new video card
- Add multiple (up to 5) monitors / projectors to your computer setup using one USB2VGAE3 device for each additional display
- View large or multiple spreadsheets across multiple displays
- A compact, lightweight solution for traveling business associates using laptop PCs enabling connection to a secondary display
- Connect multiple monitors to a single computer to create engaging multimedia presentations

- Use the adapter to connect your PC to your television for showing family pictures and movies
- Increase productivity by running multiple applications on different screens, check your email on one display and work on a document in the other
- Great for researchers and writers offering the ability to have reference material on one display and a working document copy on the other

Features

- No power adapter required
- Supports resolutions up to 1920x1200
- Works with desktop and laptop computers
- Simple installation
- Small form factor

| | | |
|---------------------|------------------------|--|
| Hardware | Warranty | 2 Years |
| | AV Input | USB 2.0 |
| | AV Output | VGA |
| | USB Pass-Through | No |
| | Memory | 32MB |
| | Industry Standards | USB 2.0 Compliant |
| | Chipset ID | Trigger - T2-285A |
| Performance | Supported Resolutions | Widescreen(16/32 bit): |
| | Wide Screen Supported | 1920x1200, 1920x1080, 1680x1050, 1600x900, 1440x900, 1360x768, 1280x800, 1280x768, 1280x720 |
| | General Specifications | |
| | MTBF | Standard(16/32 bit): 1600x1200, 1400x1050, 1280x1024, 1280x960, 1152x864, 1024x768, 800x600 Yes This USB video adapter uses a Trigger family chipset. If you're connecting this device to a computer along with additional USB video adapters or docking stations, please avoid using devices with a DisplayLink or Fresco family chipset. 200,000 Hrs |
| Connector(s) | Connector A | USB Type-A (4 pin) USB 2.0 |
| | Connector B | VGA (15 pin, High Density D-Sub) |
| Software | OS Compatibility | Windows 10 (32/64) Windows 8 / 8.1 (32/64) |

Windows 7(32/64)

Windows Vista (32/64)

Windows XP (32/64)

| | | |
|-------------------------------------|-------------------------------|--|
| Special Notes / Requirements | System and Cable Requirements | System Processor: Quad Core 2.4GHz (i5 recommended) |
| | Note | System Memory: 4GB |
| | Note | This USB video adapter uses a Trigger family chipset. If you're connecting this device to a computer along with additional USB video adapters or docking stations, avoid using devices with different family chipsets, such as DisplayLink or Fresco Logic |
| | Note | Connect a maximum of five USB video adapters on a single computer. Support for multiple adapters will vary depending upon your system resources This USB video adapter is not intended for graphical intensive applications, such as gaming |
| Environmental | Operating Temperature | -10C to 55C (14F to 131F) |
| | Storage Temperature | -25C to 75C (32F to 167F) |
| | Humidity | 0~95% RH Non-condensing |
| Physical Characteristics | Color | Gray |
| | Cable Length | 19.7 in [5 cm] |
| | Product Length | 3.5 in [88 mm] |
| | Product Width | 2.1 in [52.5 mm] |
| | Product Height | 0.7 in [18 mm] |
| | Weight of Product | 3.3 oz [94 g] |
| Packaging Information | Package Length | 8.3 in [2.1 cm] |
| | Package Width | 5.7 in [1.4 cm] |
| | Package Height | 1.6 in [40 mm] |
| | Shipping (Package) Weight | 8.7 oz [247 g] |
| What's in the Box | Included in Package | Driver and Software CD |
| | Included in Package | USB to VGA Adapter |
| | Included in Package | Instruction Manual |

****Product appearance and specifications are subject to change without notice.***

