

Professional USB to VGA External Dual or Multi Monitor Video Adapter

Product ID: USB2VGAPRO



The USB2VGAPRO Professional USB VGA External Dual or Multi Monitor Video Adapter is the perfect solution for turning your workstation into a dual or multi-monitor environment using your USB ports - providing high quality, dual display or multi-monitor capability for a variety of laptop or desktop applications.

With improved performance compared to our USB2VGA and USB2VGA2, this USB VGA display adapter is capable of running up to five additional displays from one computer simultaneously (using four USB2VGAPRO External Multi Monitor Video Adapters). The adapter connects to a host computer through a USB 2.0 port, acting as an external VGA video card to either extend or mirror the desktop shown on the existing display - without having to open the computer case.

USB2VGAPRO offers support for Microsoft Windows (including Aero themes) and Mac OS X, and with support for resolutions up to 1920x1200 this device is ideal for larger displays / monitors.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Can't install a new or additional video card? No problem, the USB2VGAPRO uses USB ports to add VGA connectivity to your PC or Mac
- Add multiple (up to five) monitors / projectors to your computer setup using one USB2VGAPRO device for each additional display
- View large or multiple spreadsheets across multiple displays
- Increase productivity by running multiple applications on different screens; check your email on one display while editing a document on the other
- Use the adapter to connect your PC to your television for showing family pictures and movies
- Connect multiple monitors to a single computer to create engaging multimedia presentations
- Great for researchers and writers offering the ability to have reference material on one display and a working document copy on the other

Features

- Optimal performance at 1920x1200 and ideal for use with 24" to 26" monitors or smaller
- Support for Aero themes in Windows
- Works with Mac OS X
- Connect up to five adapters to one PC for a true extended desktop experience
- USB Powered - No external power adapter required
- Quick and easy install

Hardware

| | |
|------------------|----------------------|
| Warranty | 2 Years |
| AV Input | USB 2.0 |
| AV Output | VGA |
| USB Pass-Through | No |
| Memory | 16MB |
| Chipset ID | DisplayLink - DL-195 |

Performance

| | |
|----------------------------|--------------------------|
| Maximum Analog Resolutions | 1920x1200 (32-bit Color) |
|----------------------------|--------------------------|

| | |
|-----------------------|---|
| Supported Resolutions | Standard(16/32 bit): |
| | 640x480, 800x600, 1280x1024, 1024x768, 1600x1200 |
| | Widescreen(16/32 bit): |
| | 1366x768, 1440X900, 1680x1050, 1920x1280, 1920x1200 |
| Wide Screen Supported | Yes |

Connector(s)

| | |
|-------------------|--------------------------------------|
| Connector Type(s) | 1 - USB 2.0 Type-A (4 pin, 480Mbps) |
| | 1 - VGA (15 pin, High Density D-Sub) |

Software

| | |
|------------------|--|
| OS Compatibility | Windows XP, Vista, 7, 8/8.1, 10 |
| | macOS 10.6 - 10.11, 11.0, 12.0, 13.0, 14.0, 15.0 |
| | Chrome OS v51 |
| | Ubuntu 14.04, 16.04, 18.04 |

Special Notes / Requirements

| | |
|-------------------------------|---|
| System and Cable Requirements | System Processor: 1.2GHz System Memory: 512MB |
| Note | Power PC-based Macintosh computers, such as late-model iMacs, PowerBooks and PowerMacs, are not currently supported This USB video adapter uses a DisplayLink family chipset. If you're connecting this device to a computer along with additional USB video adapters or docking stations, avoid using devices with different family chipsets, such as Trigger or Fresco Logic Connect a maximum of five USB video adapters on a single computer. Support for multiple adapters will vary depending upon your system resources This USB video adapter is not intended for graphical intensive applications, such as gaming |

Indicators

| | |
|----------------|------------------|
| LED Indicators | 1 - Blue - Power |
|----------------|------------------|

Physical Characteristics

| | |
|-------------------|-----------------|
| Color | Black |
| Product Length | 3.5 in [90 mm] |
| Product Width | 1.9 in [4.8 cm] |
| Product Height | 0.9 in [2.4 cm] |
| Weight of Product | 2.6 oz [73 g] |

Packaging Information

| | |
|---------------------------|------------------|
| Package Length | 6.4 in [16.3 cm] |
| Package Width | 2.5 in [62.5 mm] |
| Package Height | 5.7 in [14.4 cm] |
| Shipping (Package) Weight | 0.6 lb [0.2 kg] |

What's in the Box

| | |
|---------------------|------------------------|
| Included in Package | 1 - USB to VGA Adapter |
| | 1 - Driver CD |
| | 1 - Instruction Manual |

****Product appearance and specifications are subject to change without notice.***