

USB 3.1 (10Gbps) Adapter Cable for 2.5" SATA Drives

Product ID: USB312SAT3CB



Here's a fast, easy way to access data on a 2.5" solid-state or hard drive. This cable-style adapter lets you connect your laptop or desktop computer directly to a solid-state drive and access it through ultra-fast USB 3.1 Gen. 2 (up to 10 Gbps).

With the adapter cable, you can quickly swap hard drives without having to install your drives into an enclosure. You can copy or retrieve data from a 2.5" SSD/HDD quickly with no additional accessories required. It gives you easy drive access for data migration, drive cloning and data backup applications, with the fast performance of USB 3.1 Gen 2.

USB 3.1 Gen 2 gives you greater bandwidth and speed with rates of up to 10 Gbps - twice the speed of USB 3.0 (USB 3.1 Gen 1) technology. It lets you leverage the high performance of the latest SSDs and hard drives, while alleviating bottlenecks in your data transfers.

This cable-style adapter features a compact, lightweight design that tucks easily into a laptop bag or carrying case. Use it wherever you go to access valuable data quickly - with no external power required.

Note: This product is not compatible with 3.5 in. hard drives. For 3.5 in. drive support, please see our USB to SATA Cable with Supplemental Power (USB312SAT3).

The USB312SAT3CB is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Technicians who need a quick, easy way to access data on 2.5" hard drives
- Take advantage of the faster speed of USB 3.1 Gen 2 (10 Gbps)

- Access any 2.5" hard drive or solid-state drive from any USB enabled computer, for data migration or drive cloning
- Back up important data to an external storage device
- Retrieve data from an old SATA drive

Features

- Get fast, temporary access to data with a USB 3.1 Gen 2 (10 Gbps) cable-style adapter
- Connects to a 2.5" SATA SSD/HDD with no accessories required
- Supports SATA I, II, III (up to 6 Gbps)
- Powered directly from the USB port
- UASP support for enhanced performance
- Backward compatible with USB 3.0, 2.0 and 1.x

Hardware

Warranty	2 Years
Interface	USB 3.1 Gen 2
Bus Type	USB 3.1 Gen 2
Number of Drives	1
Drive Size	2.5in
Compatible Drive Types	SATA
Number of 2.5 inch bays	1
Chipset ID	ASMedia - ASM235CM

Performance

Maximum Data Transfer Rate	10 Gbps
Type and Rate	USB 3.1 Gen 2 - 10 Gbit/s
UASP Support	Yes
TRIM Support	Yes
4Kn Support	Yes



Hardware Raid Supported	No
Max Drive Capacity	Currently tested with hard drives up to 2TB at 7200 RPM
Hot Swap Capability	Yes
MTBF	1,665,032 hours

Connector(s)

Drive Connectors	SATA Data & Power Combo (7+15 pin)
Host Connectors	USB 3.1 USB Type-A (9 pin, Gen 2, 10 Gbps)

Software

OS Compatibility	OS independent; No software or drivers required
------------------	---

Special Notes / Requirements

Note	Windows 7 and earlier Windows versions do not support TRIM with USB to SATA devices.
------	--

Power

Power Source	USB-Powered
--------------	-------------

Environmental

Operating Temperature	0C to 70C (32F to 158F)
Storage Temperature	-10C to 55C (14F to 131F)
Humidity	40% ~ 50% RH

Physical Characteristics

Color	Black
Material	Plastic
Product Length	20.3 in [51.5 cm]
Product Width	1.8 in [45 mm]
Product Height	0.3 in [8 mm]
Weight of Product	1.1 oz [30.5 g]

Packaging



Information

Package Length	8.7 in [22 cm]
Package Width	7.8 in [19.8 cm]
Package Height	0.4 in [10 mm]
Shipping (Package) Weight	2.0 oz [56 g]

What's in the Box

Included in Package	USB 3.1 to SATA 2.5" HDD adapter cable
	quick start guide

****Product appearance and specifications are subject to change without notice.***

