

3.3ft (1m) USB-C Cable, USB 10Gbps, 60W (3A) Power Delivery, 8K 60Hz / 4K 144Hz DP Alt Mode, USB-IF Certified - Thunderbolt Compatible

Product ID: USB31CC1M



This USB-C to USB-C cable lets you connect a USB 3.2 Gen 2, USB Type-C device, such as a hard drive or mobile device, to the USB-C port on your computer, charger or tablet. The cable is also compatible with Thunderbolt 3 ports.

This 1-meter cable lets you charge or sync your mobile devices with your laptop or desktop computer. Moving large files or transferring movies can be done in seconds, at twice the speed of USB 3.2 Gen 1 and 20x faster than USB 2.0 -- all while charging your device with 60 watts (3 amps) power delivery.

You can also use the cable to charge your devices from a USB-C wall charger, car charger or power bank -- perfect for people on the move, for providing simple, tidy connections.

You'll also be able to connect your USB 3.2 Gen 2 peripheral devices, such as hard drive enclosures and docks, to your laptop. With a bandwidth of 10Gbps, this USB 3.2 Gen 2 cable lets you sync your USB Type-C devices in no time at all. You can spend less time transferring and backing up your data and more time focusing on your projects and presentations.

The cable supports full 4K 60Hz video and DisplayPort 1.2 and is compatible with existing DisplayPort displays. It's ideal for connecting your docking station or laptop to a monitor with astonishing resolution, contrast, and color depth for amazing detail.

This USB-C cable has been certified with USB-IF (USB Implementers Forum) in order to meet all USB 3.2 Gen 2 specifications. This includes all environmental, electrical and mechanical standards set by USB compliance. This ensures a high-quality, reliable cable for all your USB-C devices.

Certifications, Reports and Compatibility



Applications

- Connect USB 3.1 devices (portable hard drives, docking stations) to a USB 3.1 capable laptop or desktop computer
- Charge and sync your USB 3.1 mobile digital devices

Features

- USB-IF Certified
- Download movies, back up your files, and sync your mobile devices faster with data transfer rates up to 10Gbps (USB 3.2 Gen 2)
- Thunderbolt 3 port compatible
- Connect more simply with reversible USB Type-C connectors, which can plug into your devices with either side facing up
- Guaranteed reliability with our 2-year warranty

Hardware

Warranty	2 Years
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

Performance

Maximum Digital Resolutions	4K @ 60Hz
Type and Rate	USB 3.2 Gen 2 - 10 Gbit/s

Connector(s)

Connector A	1 - USB 3.2 Type-C (24 pin, Gen 2, 10Gbps)
Connector B	1 - USB 3.2 Type-C (24 pin, Gen 2, 10Gbps)

Power

Power Delivery	60W
----------------	-----

Physical Characteristics

Color	Black
Connector Style	Straight
Cable Length	3.3 ft [1 m]
Product Length	3.3 ft [1.0 m]
Product Width	0.5 in [1.2 cm]
Product Height	0.3 in [0.6 cm]
Weight of Product	1.7 oz [48 g]

Packaging Information

Package Quantity	1
Package Length	8.7 in [22.0 cm]
Package Width	4.9 in [12.5 cm]
Package Height	0.6 in [1.5 cm]
Shipping (Package) Weight	1.8 oz [52.0 g]

What's in the Box

Included in Package	1 - 1m USB 3.1 USB-C Cable
---------------------	----------------------------

**Product appearance and specifications are subject to change without notice.*